

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / black, 1 m

CORNING

The black FutureCom™ Cat.6 patch cords with 2x RJ45 plugs in compliance with IEC 60603-7-5 Ed.1.0 provide transmission performance according to Category 6 specifications of ISO/IEC 11801 Ed.2.2 and EN 50173 (series).

FutureCom cables are low skew products, i.e. the difference in propagation delay between the individual pairs is very low, an increasing requirement for Gigabit Ethernet. The suitability of the cable for high-bit-rate transmission systems ensures a high degree of future proofing throughout the system.

The RJ45 connectors are fully assigned and hence application independent. Additional features are the slim design and low weight of the flex cables. Each pair is individually shielded with foil (FTP). FutureCom™ Cat.6 patch cords provide additional latch protection through the different coloured boot options available.

## Features

- RJ45 to RJ45 according to IEC 60603-7-5 (2010-04) Ed. 2.0
- Application independent, all four pairs terminated
- Halogen-free (LS0H/LSZH), flame-retardant
- Coloured latch protection
- Supports Gigabit Ethernet
- Category 6 component



Part Number: CCAEIA-DU002-A010-C0



Part Number: CCAEIA-DU002-A010-C0

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / black, 1 m

CORNING

## Specifications

### General Specifications

Cable assembly type	Patch Cords
Environment	Indoor
Cable type	U/FTP
Halogen-free	Yes
Category	6

### Design - Connector A

Connector Type	RJ45 - 8/8
----------------	------------

### Mechanical Specifications - Connector A

Durability	750 Cycles
------------	------------

### Electrical Specifications - Connector

Insulation Resistance	> 5000 MΩ
-----------------------	-----------

### Design - Connector B

Connector Type	RJ45 - 8/8
----------------	------------

### Cable design

Outer diameter	5.5 mm
Min. Bend Radius Installation	30 mm
Min. Bend Radius Operation	20 mm
No. of pairs	4
Outer jacket material	LSZH™/FRNC
Outer jacket colour	black

### Mechanical Characteristics

Conductor Insulation	Foam Skin PE
Copper conductor	AWG26 stranded

# FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector

black / black, 1 m

CORNING

## Mechanical Characteristics

Operating temperature	-20 °C to 60 °C
Fire Load	0.43 MJ/m

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Ordering Information

Part Number	CCAIEA-DU002-A010-C0
Product Description	FutureCom™ E Patch Cord, FRNC, RJ45 - RJ45 connector, cable black, boot black, 1 m
EAN Code	4042673606970
Colour	Black / Black
Weight	0.05 kg
Length	1 m

## Shipping Information

Units Per Delivery	1/1
--------------------	-----



Corning Optical Communications GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY  
00 800 2676 4641 · FAX: +49 30 5303 2335 · [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2016 Corning Optical Communications. All rights reserved.