

12-fibre MTP® Jumper

50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned),
TIA-568 Type-B polarity, no pulling grip, LSZH, 3 m

CORNING

EDGE™ 40G multimode patch cables allow for the seamless migration to higher data rates in the data centre when used in conjunction with our universal trunks. This patch cable is based around pinned or non-pinned 12-fibre MTP connectors.

Features and Benefits

Factory-terminated solutions

Provide consistent quality, ensure system performance, and reduce installation time

Low insertion loss performance

Allows for more connections in a link when deploying a TIA-942-compliant system



Part Number: J757512QEZ-NB003M

Specifications

General Specifications

Application	Data Centre LAN/SAN
Flame rating	LSZH™/FRNC
Cable type	Interconnect
Fibre Category	50 µm MM (OM4)

Temperature Range

Operation	-10 °C to 60 °C (14 °F to 140 °F)
-----------	-----------------------------------

Design - Connector A

Connector Type	MTP® (non-pinned)
Ferrule Material	Composite
Polish	PC
Housing material	Composite
Housing Colour	black
Boot type	Individual
Boot colour	turquoise
Keyed (security)	No

12-fibre MTP® Jumper

50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned),
TIA-568 Type-B polarity, no pulling grip, LSZH, 3 m

CORNING

Mechanical Specifications - Connector A

Durability	≤ 0.2 dB 200 rematings, FOTP-21
Tensile strength jacketed cable	10 N

Optical Specifications - Connector A

Insertion loss, max.	0.25 dB
Reflectance	≤ -20 dB

Design - Connector B

Connector Type	MTP® (non-pinned)
Ferrule Material	Composite
Polish	PC
Housing material	Composite
Housing Colour	black
Boot type	Individual
Boot colour	turquoise
Keyed (security)	No

Mechanical Specifications - Connector B

Durability	≤ 0.2 dB 200 rematings, FOTP-21
Tensile strength jacketed cable	10 N

Optical Specifications - Connector B

Insertion loss, max.	0.25 dB
Reflectance	≤ -20 dB

Cable design

Fibre Count	12
Outer diameter	2.0 mm
Outer jacket colour	turquoise
Outer jacket material	LSZH™/FRNC
Minimum Bend Radius	17 mm

12-fibre MTP® Jumper

50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned),
TIA-568 Type-B polarity, no pulling grip, LSZH, 3 m

CORNING

Cable design

Crush resistance (reversible)	750 N/10 cm
Tensile strength	200 N

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	-----------------------------------------------------------

Ordering Information

Part Number	J757512QEZ-NB003M
Product Description	12-fibre MTP® Jumper, 50 µm multimode (OM4), MTP (non-pinned) to MTP (non-pinned), TIA-568 Type-B polarity, no pulling grip, LSZH, 3 m
EAN Code	4042673584575
Length	3 m
Weight	0.0206 kg

Shipping Information

Packing type	Cardboard box
Packing dimensions (L x W x H)	380 mm x 250 mm x 180 mm
Units Per Delivery	1/1



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.