



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW

SHOWN W/O DUSTCAPS


SEE SHEETS 2 THRU 5
FOR ARTWORK DETAILS

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS:
 - A. SEE SHEET 2 FOR METHOD B, END 1.
 - B. SEE SHEET 3 FOR METHOD B, END 2.
 - C. SEE SHEET 4 FOR KEYED METHOD B, END 1.
 - D. SEE SHEET 5 FOR KEYED METHOD B, END 2.
4. METHOD B CASSETTES COMPLY WITH ANSI/TIA-568-C.0. SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND EXAMPLES OF B BASIC LINKS.
5. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
6. CASSETTE WEIGHT: 4.16oz [118g]
7. DIMENSIONS IN BRACKETS ARE METRIC.



KEY UP TO KEY UP
MTP/MPO ADAPTER

							TITLE 12 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AW/01			PANDUIT		
							DATASET FILE NAME 10F113AW_DC-12/01A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
							THIRD ANGLE PROJECTION					
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-12				MATERIAL: SEE NOTES		
										DRAWING NUMBER: 10F113AW-DC-12		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
							SAT	11-26-13	YMG	NONE	SHT 1 OF 5	A


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX LC CASSETTE - METHOD B, END 1

PART NUMBER	DESCRIPTION
FC2ZO-12-10B1	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-10B1	12 FIBER 50/125um OM4
FC2XO-12-10B1	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-10B1	12 FIBER 50/125um OM3
FC25N-12-10B1	12 FIBER 50/125um OM2
FC26N-12-10B1	12 FIBER 62.5/125um OM1
FC29N-12-10B1	12 FIBER 9/125um OS1/OS2
FC2SA-12-10B1	12 FIBER 50/125um OM4+, SIGNATURE CORE



METHOD B, END 1 - FIBER LAYOUT


										TITLE 12 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING		
										ITEM REVISION NAME 10F113AW/01		
										DATASET FILE NAME 10F113AW_DC-12/01A		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION		MATERIAL: SEE NOTES SHEET 1
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION				10F113AW-DC-12	DRAWING NUMBER: 10F113AW-DC-12		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 5	SIZE A

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX LC CASSETTE - METHOD B, END 2	
PART NUMBER	DESCRIPTION
FC2ZO-12-10B2	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-10B2	12 FIBER 50/125um OM4
FC2XO-12-10B2	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-10B2	12 FIBER 50/125um OM3
FC25N-12-10B2	12 FIBER 50/125um OM2
FC26N-12-10B2	12 FIBER 62.5/125um OM1
FC29N-12-10B2	12 FIBER 9/125um OS1/OS2
FC2SA-12-10B2	12 FIBER 50/125um OM4+, SIGNATURE CORE



METHOD B, END 2 - FIBER LAYOUT


							TITLE 12 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING						
							ITEM REVISION NAME 10F113AW/01						
							DATASET FILE NAME 10F113AW_DC-12/01A						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °				MATERIAL: SEE NOTES SHEET 1		
							 THIRD ANGLE PROJECTION				DRAWING NUMBER: 10F113AW-DC-12		
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-12	DRAWN BY SAT		DATE 11-26-13	CHK YMG	SCALE NONE	SHT 3 OF 5	SIZE A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN							

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX COLORED/KEYED LC CASSETTE - METHOD B, END 1

PART NUMBER	DESCRIPTION
FC2ZO-12-**B1	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-**B1	12 FIBER 50/125um OM4
FC2XO-12-**B1	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-**B1	12 FIBER 50/125um OM3
FC25N-12-**B1	12 FIBER 50/125um OM2
FC26N-12-**B1	12 FIBER 62.5/125um OM1
FC29N-12-**B1	12 FIBER 9/125um OS1/OS2
FC2SA-12-**B1	12 FIBER 50/125um OM4+, SIGNATURE CORE

** - INDICATES CHARACTERS REPRESENTING KEYED & NON-KEYED
LC ADAPTERS WITH RESPECTIVE COLORS.



METHOD B, END 1 - FIBER LAYOUT (COLORED/KEYED)


							TITLE 12 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AW/01					
							DATASET FILE NAME 10F113AW_DC-12/01A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±				MATERIAL: SEE NOTES SHEET 1	
							 THIRD ANGLE PROJECTION				DRAWING NUMBER: 10F113AW-DC-12	
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-12						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX COLORED/KEYED LC CASSETTE - METHOD B, END 2

PART NUMBER	DESCRIPTION
FC2ZO-12-**B2	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-**B2	12 FIBER 50/125um OM4
FC2XO-12-**B2	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-**B2	12 FIBER 50/125um OM3
FC25N-12-**B2	12 FIBER 50/125um OM2
FC26N-12-**B2	12 FIBER 62.5/125um OM1
FC29N-12-**B2	12 FIBER 9/125um OS1/OS2
FC2SA-12-**B2	12 FIBER 50/125um OM4+, SIGNATURE CORE

** - INDICATES CHARACTERS REPRESENTING KEYED & NON-KEYED LC ADAPTERS WITH RESPECTIVE COLORS.



METHOD B, END 2 - FIBER LAYOUT (COLORED/KEYED)

							TITLE 12 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AW/01				PANDUIT	
							DATASET FILE NAME 10F113AW_DC-12/01A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					
							THIRD ANGLE PROJECTION				MATERIAL: SEE NOTES SHEET 1	
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-12					DRAWING NUMBER: 10F113AW-DC-12	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 5 OF 5	SIZE A