






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES :

1. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
2. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
3. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.

							TITLE 24 FIBER FERRULE MTP TO 24 FIBER FERRULE MTP SMALL DIAMETER TRUNK CUSTOMER DRAWING					
							ITEM REVISION NAME 12F178BJ/00					
							DATASET FILE NAME 12F178BJ_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					
							 THIRD ANGLE PROJECTION					
R	05-28-13	MC	PJI	SFDO	RELEASED TO PRODUCTION	12F178BJ-DC	DRAWING NUMBER: 12F178BJ-DC					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MC	DATE 05-05-13	CHK PJI	SCALE NONE	SHT 1 OF 2	SIZE A

B

TABLE 1 - CONNECTOR LOSS	
Connector	Loss
1	0.00
2	0.00
3	0.00
4	0.00
5	0.00
6	0.00
7	0.00
8	0.00
9	0.00
10	0.00
11	0.00
12	0.00
13	0.00
14	0.00
15	0.00
16	0.00
17	0.00
18	0.00
19	0.00
20	0.00
21	0.00
22	0.00
23	0.00
24	0.00
25	0.00
26	0.00
27	0.00
28	0.00
29	0.00
30	0.00
31	0.00
32	0.00
33	0.00
34	0.00
35	0.00
36	0.00
37	0.00
38	0.00
39	0.00
40	0.00
41	0.00
42	0.00
43	0.00
44	0.00
45	0.00
46	0.00
47	0.00
48	0.00
49	0.00
50	0.00
51	0.00
52	0.00
53	0.00
54	0.00
55	0.00
56	0.00
57	0.00
58	0.00
59	0.00
60	0.00
61	0.00
62	0.00
63	0.00
64	0.00
65	0.00
66	0.00
67	0.00
68	0.00
69	0.00
70	0.00
71	0.00
72	0.00
73	0.00
74	0.00
75	0.00
76	0.00
77	0.00
78	0.00
79	0.00
80	0.00
81	0.00
82	0.00
83	0.00
84	0.00
85	0.00
86	0.00
87	0.00
88	0.00
89	0.00
90	0.00
91	0.00
92	0.00
93	0.00
94	0.00
95	0.00
96	0.00
97	0.00
98	0.00
99	0.00
100	0.00

FIBER TYPE	MAX. IL (dB)	MAX. IL (dB)
50/125 OM3	0.50	30
50/125 OM4		
9/125 OS1/OS2	0.75	55

A