






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
WGWMTB8	.57 LBS (259 g)

NOTES

- SEE CURRENT CATALOG FOR PART NUMBER DESIGNATION FOR TYPE AND COLOR.
- WYR-GRID WALL MOUNT BRACKET MOUNTS TO A VERTICAL SURFACE, SUCH AS A WALL, TO SUPPORT WYR-GRID PATHWAY.
- EACH PACKAGE CONSISTS OF:
 - (1) WYR-GRID WALL MOUNT BRACKET
 - (2) WYR-GRID QUICK LOCK CLIP
 - (2) 1/4-20x1/2 HEX HEAD CAP SCREW
 - (2) 1/4 HELICAL SPRING LOCKWASHER
- DIMENSIONS IN PARENTHESES ARE METRIC.

							TITLE					
							WYR-GRID 8" WALL MOUNT TERMINATION BRACKET (WGWMTB8)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME		09D017IR/00			
							DATASET FILE NAME		09D017IR_DC/00A WGWMTB8			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:
							.X ± .XX ± .05 [1.3] .XXX ± ANGLES ± 5 °					STEEL
											DRAWING NUMBER:	
							THIRD ANGLE PROJECTION				09D017IR-DC	
							DRAWN BY	DATE	CHK	SCALE		SIZE
							SSP	12-05-13	DWW	NONE		A
							SHT 1 OF 1					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN						
R	12-05-13	SSP	DWW	RN	RELEASED TO PRODUCTION	09D017IR-DC						