


596-00621

Article Number: 596-00621

Pre-Printed Header Label, WARNING, 4" X 6", PET, Orange, 250/RL



Base Data

Local Order Number	596-00621
Type	4X6WARNING
Color	Orange (OG)
Features and Benefits	<ul style="list-style-type: none"><li>• Made with UV stable inks and materials for durability and weather resistance</li><li>• Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.</li><li>• High abrasion and scuff resistance for high performance labeling.</li><li>• Meets NEC &amp; IFC standards for printed text, character height, color and outdoor UV stability to pass inspections</li></ul>
Product Description	HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Short Description	Pre-Printed Header Label, WARNING, 4" X6", PET, Orange, 250/RL

Product Dimensions

Length L (Imperial)	4.0 "
Length L (Metric)	101.6 mm
Width W (Imperial)	4.0 "
Width W (Metric)	101.6 mm
Height H (Imperial)	6.0 "
Height H (Metric)	152.4 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	250
Package Quantity (Metric)	250
Labels per Column	1
Labels per Row	1
Weight (imperial)	31.97 oz

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Adhesive	Acrylic

**Adhesive Shortcut** Acrylic

**Adhesive Operating Temperature** -40°F to +302°F (-40°C to +150°C)

**Halogenfree** Yes

**Operating Temperature** -40°F to +302°F (-40°C to +150°C)

**ROHS Compliant** Yes

**UL Recognized (US)** Yes