

2



1





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
V1B2B1L2N30AHA0	7.1kg (15.60lbs)


NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C13 & (6) C19, BASIC 208V / 30A / SINGLE-PHASE PDU

PART NO. V1B2B1L2N30AHA0
COLOR BLACK


2. ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
4. RoHS COMPLIANT.
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
6. MAXIMUM AVAILABLE INPUT POWER = 4.9 kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
8. PRINTED WITH PHASE & CIRCUIT IDENTIFICATION.



PLUG
30 AMP, 250V
TWIST-LOCK
NEMA L6-30P



TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
20 AMP, 230V
STRAIGHT BLADE
IEC 60320/C19

01A	09-18-14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V091X0-DC

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE BASIC PDU (24) C13 & (6) C19 CUSTOMER DRAWING			
ITEM REVISION NAME 12V091X0/01			
DATASET FILE NAME 12V091X0_DC/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		METRIC - MILLIMETER X.X +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18	
ANGLE +/- 1°		MATERIAL/COLOR: N/A	
DRAWN BY SAT		DATE 09-11-14	
CHK MRWA		SCALE NONE	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 12V091X0-DC	
SHT 1 OF 1		SIZE B	