


PANDUIT P/N	WEIGHT
GM-A0937BL	10 kg (22 lb)

NOTES:
1. IDENTIFICATION: GATEWAY MONITORED 2RU INLINE METER,
(1) 20A IEC60309, 208V / 20A / THREE-PHASE PDU


PART NO. COLOR
GM-A0937BL BLACK RAL 9005

2. ACCESSORY COMPONENTS:
- (4) M6 x 12mm MOUNTING SCREWS
 - (4) M6 x 12mm MOUNTING SCREWS
 - (4) M6 NUT (CAGED)
 - (1) M5 NUT (NYLON INSERT)
 - (1) M5 LOCK WASHER


3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. PHASE (L1, L2, L3) LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 5.8 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




TOP VIEW




FRONT VIEW



SIDE VIEW





PLUG
20 AMP, 250V 3~(DELTA)
3P/4W
IEC 60309, SPLASHPROOF



RECEPTACLE
20 AMP, 250V 3~(DELTA)
3P/4W
IEC 60309, SPLASHPROOF

00A	10/16/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0937CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.				SIGN			
				DATE			
				PRINT			
TITLE SmartZone Gateway-Enabled 2RU Inline Meter PN: GM-A0937BL CUSTOMER DRAWING							
ITEM REVISION NAME AA0937CP/00.PRT							
DATASET FILE NAME AA0937CP_DS/00A.PRT							
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:						MATERIAL/COLOR: BLACK RAL 9005 TEXTURE FINISH	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XX +/- 0.007			METRIC - MILLIMETER X.X +/- 0.8 X.XX +/- 0.46 X.XX +/- 0.18		ANGLE +/- 1°		
			THIRD ANGLE PROJECTION		DRAWING NUMBER: AA0937CP		
DRAWN BY DACU		DATE 10/16/14		CHK JPHI	SCALE SCALE:1:7		
					SHEET 1 OF 1		
					SIZE B		