



760082495 | RK6-45A

**6 in (152 mm) Channel x 7 ft (2134 mm) H - 19 in (482.6 mm) AI Equipment Rack (45U)
12-24 Tapped Rails, Black**

Dimensions

Channel Width	6.0 in
Depth	457.2 mm 18.0 in
Dimensional Standards	EIA-310-E
Height	2133.6 mm 84.0 in
Weight	13.61 kg 30.00 lb
Width	518.2 mm 20.4 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Product Type	2 post rack
Rack Units	45
Color	Black
Finish	Powder-coated, textured
Includes	Forty #12-24 x 1/2 in mounting screws Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8-16 hex nuts Twelve 3/8-16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Two vertical rack rails
Package Quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

Mechanical Specifications

Rail Mounting Hole	#12-24
Material Type	Aluminum
Static Load Rating	453.6 kg 1000.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

