



TOP VIEW



FRONT VIEW



SIDE VIEW


Panduit P/N	Weight
GM-A0949BL	8.5 kg (19 lb)

NOTES:  
1. IDENTIFICATION: GATEWAY MONITORED 1 RU INLINE METER,  
(1) NEMA L6-30P 208V 30A / SINGLE PHASE PDU


PART NO. GM-A0949BL  
COLOR BLACK RAL 9005

2. ACCESSORY COMPONENTS:
- (4) M6 x 12mm PAN HEAD MACHINE SCREWS
  - (4) M6 x 12mm PAN HEAD SELF-TAPPING SCREWS
  - (4) M6 NUT (CAGED)
  - (1) M5 NUT (NYLON INSERT)
  - (1) M5 LOCK WASHER

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]  
4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.  
5. RoHS COMPLIANT.  
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS  
APPLICABLE FOR USE WITH THIS PART.  
7. MAXIMUM AVAILABLE INPUT POWER = 4.9 kW  
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



PLUG  
30 AMP 250V  
TWIST LOCK  
NEMA L6-30P



RECEPTACLE  
30 AMP 250V  
TWIST LOCK  
NEMA L6-30R

00A	10/07/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0949CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX.  
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN  
DATE  
PRINT

TITLE  
SmartZone Gateway-Enabled 1RU Inline Meter  
PN: GM-A0949BL  
CUSTOMER DRAWING


ITEM REVISION NAME  
AA0949CP/00.PRT

DATASET FILE NAME  
AA0949CP\_DS/00A.PRT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007  
METRIC - MILLIMETER X.X +/- 0.8 X.X +/- 0.46 X.XXX +/- 0.18  
ANGLE +/- 1°

MATERIAL/COLOR:  
BLACK RAL 9005  
TEXTURE FINISH

DRAWING NUMBER:  
AA0949CP

THIRD ANGLE PROJECTION

DRAWN BY  
DACU

DATE  
10/07/14

CHK  
JPHI

SCALE  
SCALE:1:7

SHEET 1 OF 1

SIZE  
B

