



760082578 | RK4P52-36A

**36 in (914 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Al Equipment Rack (52U) 12-24 Tapped Rails, Black**

## Dimensions

Channel Width	3.0 in
Depth	1219.2 mm   48.0 in
Dimensional Standards	EIA-310-E
Height	2438.4 mm   96.0 in
Weight	46.27 kg   102.00 lb
Width	518.2 mm   20.4 in

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## General Specifications

Product Type	4 post rack
Rack Units	52
Color	Black
Finish	Powder-coated, textured
Includes	Base pan   Forty #12-24 x 1/2 in mounting screws   Four vertical rack rails   Instruction sheet   Twelve 3/8 in split lock washers   Twelve 3/8-16 hex nuts   Twelve 3/8-16 UNC x 1 in hex head bolts   Two extruded base angles   Two extruded top angles   Upper plate support
Package Quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

## Mechanical Specifications

Rail Mounting Hole	#12-24
Material Type	Aluminum
Static Load Rating	907.2 kg   2000.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

