

2



1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
Q1N1B1FOA30AHA0	6.97kg (15.4lb)

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19, NETWORKED 208V / 20A / SINGLE PHASE PDU

PART NO. Q1N1B1FOA30AHA0 COLOR BLACK

2. ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
4. CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED VIA ON-UNIT DISPLAY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 3.3 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



PLUG
20 AMP, 250V
TWIST LOCK
NEMA L6-20P

TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
RECEPTACLES
20 AMP, 230V
STRAIGHT BLADE
IEC 60320/C19

01A	5-15-14	PIP	MRWA	EDM	RELEASED TO PRODUCTION	12V092DG-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
Q1N1B1FOA30AHA0			
CUSTOMER DRAWING			
ITEM REVISION NAME			
12V092DG/01.PRT			
DATASET FILE NAME		MATERIAL/COLOR:	
12V092DG_DC/01A.PRT		N/A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		DRAWING NUMBER:	
INCHES +/- 0.03 METRIC - MILLIMETER ANGLE		12V092DG - DC	
X.X +/- 0.018 X.X +/- 0.8		SHT 1 OF 1	
X.XX +/- 0.007 X.XX +/- 0.46		SIZE	
X.XXX +/- 0.007 X.XX +/- 0.18		B	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
PIP	5-15-14	MRWA	NONE