



760117366 | 360-PM-GS3-2U-48P

**SYSTIMAX 360™ GigaSPEED XL® PATCHMAX® GS3 Category 6 U/UTP Patch Panel, 48 port**

- Available for use with the DYMO® labeling solution

## Dimensions

Depth, with cable management	10.50 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	88.90 mm   3.50 in
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	iPatch® ready
Total Ports, quantity	48
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	GigaSPEED XL®   PATCHMAX®   SYSTIMAX 360™   SYSTIMAX®
Color	Cool gray   Satin chrome
Modules, quantity	4
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2

## Mechanical Specifications

Panel Style	Straight
Conductor Gauge, solid	22 AWG   24 AWG
Conductor Gauge, stranded	22 AWG   24 AWG
Conductor Type	Solid   Stranded (7 strands)
Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel

# Product Specifications

760117366 | 360-PM-GS3-2U-48P

Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

