

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
Q1N2B1M2M24AKA0	7.91 kg (17.4 lb)

NOTES:  
1. IDENTIFICATION: VERTICAL, (24) NEMA 5-20R, NETWORKED 120V / 30A / SINGLE PHASE PDU


PART NO. Q1N2B1M2M24AKA0      COLOR BLACK

2. ACCESSORY COMPONENTS:  
(1) QUICK-START GUIDE
3. DIMENSIONS IN PARENTHESIS ARE IN INCHES (in).
4. CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 2.9 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.


B



BOTTOM VIEW




TOP VIEW



SIDE VIEW

A



01A	03/26/14	PJST	MRWA	EDM	RELEASED TO PRODUCTION	12V091TN-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
Q1N2B1M2M24AKA0			
CUSTOMER DRAWING			
ITEM REVISION NAME		12V091TN/01	
DATASET FILE NAME		12V091TN_DC/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	± 0.03	METRIC - MILLIMETER	ANGLE
X.X	± 0.018	X.X	± 0.8
X.XX	± 0.007	X.X	± 0.46
X.XXX		X.XX	± 0.18
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY		12V091TN-DC	
DATE		SHT 1 OF 1	
12-12-13		SIZE	
CHK		B	
MRWA			
SCALE			
1:8			