

This specification is OBSOLETE



760142927 | NC 42U 800X800 NS

Network Bay Cabinet 42U 800 mm (32 inches) Wide x 800 mm (32 inches) Deep, Steel Frame with Viewing Window Partially Perforated Front, Split Perforated Rear

OBSOLETE

This product was discontinued on: December 31, 2014

Dimensions

Depth	804.4 mm 31.7 in
Height	2000.5 mm 78.8 in
Width	797.0 mm 31.4 in
Dimensional Standards	EIA-310-E
Weight	131.50 kg 289.91 lb

General Specifications

Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada		
Rack Units	42		
Color	Black		
Finish	Powder-coated, textured		
Includes	Fifty M6 clip nuts Four M12 leveling feet One hundred M6 screws		
Package Quantity	1		
Packaging Type	Assembled		

Mechanical Specifications

Door Type, front	Single
Door Type, rear	Double
Cable Entry, top	Four openings of 4 in (100 mm), with protective covers
Door Material, front	Plexiglass
Door Material, rear	Steel
Door Vent, front	Vented/Partially perforated
Door Vent, rear	Vented/Split perforated
Frame Type	Welded
Lock Type, front	2-Point
Lock Type, rear	1-Point
Material Type	Steel
Side Panels	Not included

Product Specifications



760142927 | NC 42U 800X800 NS

Static Load Rating	1451.5 kg 3200.0 lb
Top Panel	Included
Top Panel Vent	Vented/Perforated

Packed Dimensions

Shipping Weight	108.90 kg 240.08 lb
-----------------	-----------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

