



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
Q1N2B2C3N30AHA0	13.3kg (29.3lb)

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C13 AND (6) C19, NETWORKED 208V / 60A / SINGLE PHASE PDU

PART NO. Q1N2B2C3N30AHA0
COLOR BLACK

2. ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
3. DIMENSIONS IN PARENTHESIS ARE IN INCHES (in).
4. CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 9.9 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

B



A

PLUG
60 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, WATERTIGHT

TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

02A	03/25/14	PJST	MRWA	EDM	RELEASED TO PRODUCTION	12V091SW-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.

THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN

DATE

PRINT

TITLE

Q1N2B2C3N30AHA0

CUSTOMER DRAWING

ITEM REVISION NAME
12V091SW/02

DATASET FILE NAME
12V091SW_DC/02A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007
METRIC - MILLIMETER X.X +/- 0.8 X.XX +/- 0.46 X.XX +/- 0.18
ANGLE +/- 1°

THIRD ANGLE PROJECTION

DRAWN BY TWV DATE 12-12-13 CHK MRWA SCALE 1:8

MATERIAL/COLOR:
N/A

DRAWING NUMBER:
12V091SW-DC

SHT 1 OF 1

SIZE
B

