






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
V1B2B4E3N30AEA0	8.8kg (19.45lbs)

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (18) C13, (6) C19 & (6) 5-20R, BASIC 120 / 208V / 30A / THREE-PHASE WYE PDU

PART NO. V1B2B4E3N30AEA0 COLOR BLACK

2. ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
4. RoHS COMPLIANT
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
6. MAXIMUM AVAILABLE INPUT POWER = 8.6kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
8. PRINTED WITH PHASE & CIRCUIT IDENTIFICATION.



PLUG
30 AMP, 120/208V × 3~ WYE
TWIST-LOCK
NEMA L21-30P

EIGHTEEN (18)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

SIX (6)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

02A	09-19-14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V091XZ-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
BASIC PDU (18) C13, (6) C19 & (6) 5-20R CUSTOMER DRAWING			
ITEM REVISION NAME		12V091XZ/02	
DATASET FILE NAME		12V091XZ_DC/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	ANGLE	
X.X +/- 0.03	X. +/- 0.8	+/- 1°	
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY SAT		12V091XZ-DC	
DATE 09-16-14	CHK MRWA	SCALE 1:8	SIZE B
SHT 1 OF 1			