



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 130mm [5.1in] TO 422mm [16.6in], AND FROM 469mm [18.46in] TO 751mm [29.56in]. WITH NO FINGERS OR POU'S, 913mm [35.94in] TO 964mm [37.95in].
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
-BASE CABINET
OPTIONAL COMPONENTS:
-FRONT PERFORATED DUAL HINGE DOOR (SEE CHART ON SHEET 2)
-SOLID SEALED REAR DOOR (SEE CHART ON SHEET 2)
-#12-24 TAPPED EQUIPMENT RAILS FRONT & REAR
-SPLIT SIDE PANELS (SEE CHART ON SHEET 2)
-VERTICAL CABLE MANAGEMENT FINGERS (SEE CHART ON SHEET 2)
-(8)BEZELS & BLANKS
-CABINET HARDWARE KIT
-INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING: 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING: 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 992mm [39.06].

01A	12-08-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00B	7-15-14	TWV			DRAWING UPDATE	12V343SQ-DC	
00A	2-19-13	TWV	JDW	JDWE	RELEASED TO PRODUCTION	12V343SQ-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		NET-ACCESS N TYPE VED READY CABINET 800mm WIDE X 1200mm DEEP FAMILY	
		CUSTOMER DRAWING	
ITEM REVISION NAME		12V343SQ/01.PRT	
DATASET FILE NAME		12V343SQ_DC/01A.PRT	
		MATERIAL:	
		N/A	
		DRAWING NUMBER:	
		12V343SQ-DC	
DRAWN BY		DATE	CHK
TWO		2-19-13	JDW
SCALE		NONE	
SHT 1 OF 5		A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	DUAL HINGE DOOR	SOLID REAR DOOR	CABLE MGMT FINGERS SET	SPLIT SIDE PANEL	TAPPED E-RAIL	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
N8222*V	NET-ACCESS N-TYPE VED READY CABINET 42RUX1200mm DEEP	01	01	02	02	02	137 Kg/EACH 303 LBS/EACH	158 Kg/EACH 348 LBS/EACH
N8522*V	NET-ACCESS N-TYPE VED READY CABINET 45RUX1200mm DEEP	01	01	02	02	02	147 Kg/EACH 325 LBS/EACH	168 Kg/EACH 370 LBS/EACH
N8822*V	NET-ACCESS N-TYPE VED READY CABINET 48RUX1200mm DEEP	01	01	02	02	02	157 Kg/EACH 347 LBS/EACH	178 Kg/EACH 392 LBS/EACH
N8229*V	NET-ACCESS N-TYPE VED READY CABINET 42RUX1200mm DEEP	01	01	02	00	02	101 Kg/EACH 223 LBS/EACH	121 Kg/EACH 268 LBS/EACH
N8529*V	NET-ACCESS N-TYPE VED READY CABINET 45RUX1200mm DEEP	01	01	02	00	02	108 Kg/EACH 238 LBS/EACH	128 Kg/EACH 283 LBS/EACH
N8829*V	NET-ACCESS N-TYPE VED READY CABINET 48RUX1200mm DEEP	01	01	02	00	02	115 Kg/EACH 253 LBS/EACH	135 Kg/EACH 298 LBS/EACH

* DENOTES COLOR

"B" = BLACK

"W" = WHITE

TITLE

NET-ACCESS N TYPE VED READY CABINET
800mm WIDE X 1200mm DEEP FAMILY

CUSTOMER DRAWING

ITEM REVISION NAME

12V343SQ/01.PRT

DATASET FILE NAME

12V343SQ_DC/01A.PRT


PANDUIT

MATERIAL :

N/A

DRAWING NUMBER:

12V343SQ-DC



THIRD ANGLE
PROJECTION

DRAWN BY

DATE

CHK

SCALE

SIZE

TWV

2-19-13

JDW

NONE

SHT 2 OF 5

A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1269
[50.0]

798
[31.4]

HEIGHT
WITHOUT
CASTERS

42RU
2000
[78.8]

45RU
2134
[84.0]

48RU
2267
[89.3]

1220 [48.0]
TILE COVERAGE
DEPTH

47 FRONT
[1.9] DOOR
DEPTH

LEFT VIEW

FRONT VIEW

RIGHT VIEW

REAR VIEW

ADD 26mm [1.0"] TO CABINET'S HEIGHT FOR CASTERS

TITLE

NET-ACCESS N TYPE VED READY CABINET
800mm WIDE X 1200mm DEEP FAMILY

CUSTOMER DRAWING

ITEM REVISION NAME

12V343SQ/01.PRT

DATASET FILE NAME

12V343SQ_DC/01A.PRT


PANDUIT

MATERIAL:

N/A

DRAWING NUMBER:

12V343SQ-DC



THIRD ANGLE
PROJECTION


01A	12-08-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00B	7-15-14	TWV			SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC
00A	2-19-13	TWV	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DRAWN BY	DATE	CHK	SCALE		
TWV	2-19-13	JDW	NONE	SHT 3 OF 5	A


2

1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN




01A	12-08-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	
00B	7-15-14	TWV			SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC	
00A	2-19-13	TWV	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE					
NET-ACCESS N TYPE VED READY CABINET 800mm WIDE X 1200mm DEEP FAMILY					
CUSTOMER DRAWING					
ITEM REVISION NAME					
12V343SQ/01.PRT					
DATASET FILE NAME			MATERIAL:		
12V343SQ_DC/01A.PRT					
			N/A		
			DRAWING NUMBER:		
			12V343SQ-DC		
DRAWN BY	DATE	CHK	SCALE	SIZE	
TWV	2-19-13	JDW	NONE	SHT 4 OF 5	
				A	

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TITLE
NET-ACCESS N TYPE VED READY CABINET
800mm WIDE X 1200mm DEEP FAMILY
CUSTOMER DRAWING

ITEM REVISION NAME
12V343SQ/01.PRT

DATASET FILE NAME
12V343SQ_DC/01A.PRT


PANDUIT

MATERIAL:

N/A

DRAWING NUMBER:

12V343SQ-DC



THIRD ANGLE
PROJECTION

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	12-08-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00B	7-15-14	TWV			SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC
00A	2-19-13	TWV	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V343SQ-DC

DRAWN BY	DATE	CHK	SCALE	SHT	OF	SIZE
TWV	2-19-13	JDW	NONE	5	5	A

2

1