


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	W	X	WEIGHT
PEVF6B1	6.0	2	30.91 LBS/EACH (14.02 KG/EACH)
PEVF8B1	8.0	3	31.44 LBS/EACH (14.26 KG/EACH)
PEVF10B1	10.0	4	31.92 LBS/EACH (14.48 KG/EACH)
PEVF12B1	12.0	6	32.42 LBS/EACH (14.71 KG/EACH)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) SINGLE-SIDED VERTICAL MANAGER
(1) HARDWARE KIT
(4) LEFT FINGERS
(4) RIGHT FINGERS
(2) DOOR BRACKET BASES
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 3 ROWS OF X RU 19" CEA OPENINGS.
- DOOR SOLD SEPARATELY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

TITLE				PATCHRUNNER HIGH CAPACITY VERTICAL MANAGER, SINGLE SIDED (PEVF*B1)			
CONTROL DRAWING							
ITEM REVISION NAME				11V260AR/00			
DATASET FILE NAME				11V260AR_DC/00B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				MATERIAL:			
				BACKBONE: STEEL FINGERS: ABS			
				DRAWING NUMBER:			
				11V260AR			
THIRD ANGLE PROJECTION							
DRAWN BY	DATE	CHK	SCALE				
FGR	9/18/13	BAME	NONE				
				SHT 1 OF 1			
				A			

00B	3/7/14	FGR	BAME	CMK	A. CORRECTED TITLE BLOCK	11V260AR
00A	9/18/13	FGR	BAME	CMK	INITIAL RELEASE	11V260AR
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN