




760105338 | 2091B BL 4/23 R1000

GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, blue jacket, 4 pair count, 1000 ft (305 m) length, reel

## Cross Section Drawing



## Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	FEP
Separator Material	FEP
Separator 2 Material	Polyolefin

## Dimensions

Cable Length	305 m   1000 ft
Cable Weight	40.70 lb/kft
Diameter Over Jacket	7.239 mm   0.285 in
Jacket Thickness	1.295 mm   0.051 in

## Electrical Specifications

ANSI/TIA Category	6A
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	7.61 ohms/100 m
Mutual Capacitance	6.0 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	66 %
Operating Frequency, maximum	550 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2   ISO/IEC 11801 Class EA

760105338 | 2091B BL 4/23 R1000

Dielectric Strength, minimum 1500 Vac | 2500 Vdc

## Environmental Specifications

Environmental Space	Plenum
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Smoke Test Method	CMP
UL Temperature Rating	75 °C   167 °F

## General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	Reel
Brand	GigaSPEED X10D®   SYSTIMAX®
Jacket Color	Blue
Product Number	2091B
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Separator Type	Isolator

## Mechanical Specifications

Pulling Tension, maximum 11 kg | 25 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

