


NOTES:
1. IDENTIFICATION: VERTICAL, (24) 5-20R NETWORKED
120V / 20A / SINGLE-PHASE POU



2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). AGGREGATE CURRENT MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.





5. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.

6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



01A	9-10-12	PIP	MRWA	C. UPDATED NOTE #5 & 8. D. ADDED NOTE #9. E. UPDATED DETAIL A.	09V098UN					
00B	2-1-12	MRWA	KRKE	B. ADDED OUTLET COLOR	09V098UN					
00A	12-16-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098UN					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098UN/01.PRT													
CAD FILENAME/LAYERS		09V098UN_DC/01A.PRT													
<div>PANDUIT CORP TINLEY PARK, ILLINOIS</div>															
VERTICAL, (24) 5-20R NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING															
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: <table><tr><td>INCHES</td><td>[METRIC - MILLIMETER]</td><td>ANGLE</td></tr><tr><td>X.X</td><td>X.X +/- 0.03</td><td>X.X +/- 0.8</td></tr><tr><td>X.XX</td><td>X.XX +/- 0.015</td><td>X.XX +/- 0.4</td></tr><tr><td>X.XXX</td><td>X.XXX +/- 0.005</td><td>X.XX +/- 0.13</td></tr></table>		INCHES	[METRIC - MILLIMETER]	ANGLE	X.X	X.X +/- 0.03	X.X +/- 0.8	X.XX	X.XX +/- 0.015	X.XX +/- 0.4	X.XXX	X.XXX +/- 0.005	X.XX +/- 0.13	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
INCHES	[METRIC - MILLIMETER]	ANGLE													
X.X	X.X +/- 0.03	X.X +/- 0.8													
X.XX	X.XX +/- 0.015	X.XX +/- 0.4													
X.XXX	X.XXX +/- 0.005	X.XX +/- 0.13													
DRAWN BY MAV	MAT'L:	SCALE	NONE												
DATE 12-16-10		DRAWING NO. 09V098UN	DWG B												
CHK'D		SIZE													