

# Central Tube Dielectric Armour Indoor/Outdoor Cable

1x6 G50 MMF ClearCurve® OM3 CT 3.0

CORNING

The central tube cable construction, by isolating the fibres from installations and environmental rigors, provides stable and highly reliable transmission parameters. The fibres in are colour coded for quick, easy identification.

The cable construction, based on a central buffer tube, is very compact, light and flexible, and ideal for connections requiring a moderate fiber count.

These cables are designed for installation in conduits, ducts and in-house.

## Features and Benefits

### All-dielectric cable construction

Requires no grounding or bonding

### Laminated swelling glass yarns

Improved rodent resistance and longitudinal water protection

### UV- and microbe-resistant

Can be installed in ducts or conduits

### Small diameter and bend radius

Easy installation in space-constrained areas

### Fibres colour coding to Telcordia-Bellcore

Easy identification of the individual fibres

### Waterblocking technology


OSP (outdoor) applications

### Silicon-free outer jacket

The cable jacket is free of harmful to paint structures



Part Number: 006TEU-13188A2G



Cross Section of Order Number: 006TEU-13188A2G

## Standards

### Flame Test Method

Flame retardant to IEC 60332-1-2 (single cable)

Low Smoke to IEC 61034

Zero Halogen to IEC 60754-1

Non Corrosive to IEC 60754-2

### Waterblocking

IEC 60794-1-2 F5

# Central Tube Dielectric Armour Indoor/ Outdoor Cable

1x6 G50 MMF ClearCurve® OM3 CT 3.0

CORNING

## Specifications

General Specifications	
Environment	Indoor / Outdoor
Application	Duct, Vertical Riser, General Purpose Horizontal
Cable type	Loose Tube
Product type	Dielectric armour
Flame rating	LSZH™/FRNC
Fibre category	50 µm MM (OM3)
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	U-DQ(ZN)BH
Previous part number	LCXLM1-K0006-H700
Previous coding following DIN VDE 0888-3	A-DQ(BN)H

Temperature Range	
Installation and assembly	-5 °C to 50 °C
Operation	-20 °C to 60 °C
Storage	-25 °C to 70 °C

Cable design	
Fibre count	6
Fibre colouring	Blue, orange, green, brown, grey, white
Buffer tube diameter	3 mm
Buffer tube colour	green
Tensile Strength Elements and/or Armouring - Layer 1	Laminated swelling glass yarn armour
Number of ripcords	1
Outer jacket material	Flame-retardant, non-corrosive/low-smoke, zero-halogen (FRNC/LSZH) material
Outer jacket colour	black
Outer jacket nominal thickness	1.2 mm
Cable marking	Meter    Handset    Sine    CORNING    Fibre Optic Cable Year    U-DQ(ZN)BH    6    OM3CC    CT    3.0    LSZH™/ FRNC

Mechanical Characteristics Cable	
Nominal outer diameter	6.6 mm
Weight	46 kg/km

# Central Tube Dielectric Armour Indoor/Outdoor Cable

1x6 G50 MMF ClearCurve® OM3 CT 3.0

CORNING

## Mechanical Characteristics Cable

Min. bend radius installation	130 mm
Min. bend radius operation	100 mm
Max. tensile strength for installation	1000 N
Crush resistance (reversible)	1500 N/10 cm
Fire Load	0.94 MJ/m

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

## Ordering Information

Part Number	006TEU-13188A2G
Product Description	Central Tube Dielectric Armour Indoor/Outdoor Cable 1x6 G50 MMF ClearCurve® OM3 CT 3.0
EAN Code	4042673343646

## Shipping Information

Maximum delivery length	4,000 m
-------------------------	---------



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2015 Corning Optical Communications. All rights reserved.