

D10100DB/09

2



1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

- NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (12) C-13 & (12) C-19 NETWORKED 208V / 60A / THREE-PHASE DELTA POU

PART NO.	COLOR
QZ1B2G6BN24Z1	BLACK

2. ACCESSORY COMPONENTS:
 - (4) #10-32 x 1/2" MOUNTING SCREWS
 - (4) #12-24 x 1/2" MOUNTING SCREWS
 - (2) #10-32 LOCKING COLLAR SCREWS
 - (2) L-BRACKETS


3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.
5. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 17.3 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




DETAIL A
(SCALE 4X)

PANDUIT P/N	WEIGHT
QZ1B2W6BN24Z1	17 lb (7.7 kg)

TOOLLESS MOUNTING
BUTTON 2X



TOOLLESS MOUNTING BUTTON LOCATION




REMOTE CURRENT METER
(SEE DETAIL A)




10 FOOT INLET POWER CORD


20 AMP, 2 POLE UL LISTED ELECTRO
MECHANICAL SWITCH/BREAKER
(6 PLACES)





PLUG
60 AMP, 250V x 3~ DELTA
3P/4W
IEC 60309, WATERTIGHT



TWELVE (12)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



TWELVE (12)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

								TITLE	VERTICAL, MIXED (12) C-13 & (12) C-19 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING			
								ITEM REVISION NAME	09V098RW/00.PRT			
								DATASET FILE NAME	09V098RW_DC/00A.PRT			
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				 MATERIAL: DRAWING NUMBER: 09V098RW
								INCHES	METRIC - MILLIMETER	ANGLE		
								X.X +/- 0.03	X. +/- 0.8			
								X.XX +/- 0.018	X.X +/- 0.46	+/- 1°		
								X.XXX +/- 0.007	X.XX +/- 0.18			
00A	1-15-13	MRWA	KRKE		RELEASED TO PRODUCTION		09V098RW		THIRD ANGLE PROJECTION			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MRWA	DATE 1-15-13	CHK KRKE	SCALE NONE	SHT 1 OF 1	SIZE B

2



1