

### CO<sub>2</sub> EXTINGUISHERS



**Carbon dioxide (CO<sub>2</sub>) extinguishers** are suitable for fires involving flammable liquids and electrical hazards. The non-corrosive and non-conductive qualities of carbon dioxide make it an ideal choice for dealing with fires involving electrical equipment and machinery.

The carbon dioxide used is a recovered industrial bi-product, thereby reducing the carbon levels contributing to the Greenhouse effect.



Part Number	4522122	4522150
Type	CO <sub>2</sub>	CO <sub>2</sub>
Capacity (ltr)	2	5
Full Weight (kg)	6.5	12.0
Cylinder Material	Steel	Steel
Cylinder Weight (kg)	4.5	7.0
Cylinder Height (mm)	497	675
Cylinder Diameter (mm)	120	155
Minimum Discharge (s)	8	14
Temperature Range (°c)	-30 to 60	-30 to 60
Working Pressure at 20°C	56 bar	56 bar
Test Pressure	212 bar	212 bar
Fire Rating	34B	70B
Approved to BS EN3	Yes	Yes
Marine Approved	No	No
Warranty*	5 Years	5 Years

We reserve the right to change the design and specification without prior notice. December 2012

\* if maintained by a competent person in accordance with BS 5306