



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
R2P79	25.6 LB/EACH (11.6 KG/EACH)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- CAN BE USED WITH ANY INDUSTRY STANDARD 19" COMPONENTS IN ADDITION TO ALL PANDUIT CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
- WILL HOLD UP TO 42 SINGLE RACK SPACINGS.
- EIA SPACING ON RACK: I.E., REF. HOLE SPACING ON UPRIGHT CHANNELS: .625, .625, .500, .625, .500, ETC.
- ASSEMBLY IS REQUIRED.
- RACK PART THICKNESSES:
 - UPRIGHT CHANNEL: WEB; .14 \pm .03
FLANGE; .19 \pm .03
 - TOP BRACKET: .187 \pm .03
 - BASE BRACKET: .25 \pm .03
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.
- ALL ASSEMBLY HARDWARE INCLUDED:
 - (12) 3/8-16 X 1" BLACK HEX HEAD CAP SCREW
 - (24) 3/8" PAINT PIERCING GROUNDING WASHER
 - (1) TUBE OF ANTI-OXIDIZING PASTE
 - (12) 3/8-16 BLACK HEX NUTS
 - (24) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREWS
- LOAD RATING - 1000 LBS

TITLE						6.5 FOOT CABLE MANAGEMENT RACK (R2P79)					
						CUSTOMER DRAWING					
ITEM REVISION NAME						V10687AK/02					
DATASET FILE NAME						V10687AK_DC/02A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						MATERIAL:					
.X ± .XX ±						.XXX ± ANGLES ±					
						THIRD ANGLE PROJECTION					
						DRAWING NUMBER:					
						V10687AK - DC					
DRAWN BY		DATE		CHK		SCALE				SHT 1 OF 2	
BAME		2-5-10		DPN		NONE				A	

02A	11-14-13	BAME	PM	SJAN	UPDATED VIEWS	V10687AK-DC
01A	6-22-10	BAME		CMK	ADDED SHEET AND DIMS	V10687AK-DC
00A	2-5-10	BAME	DPN	CMK	DRAWING RELEASED	V10687AK-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

B

A





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
R2P79	25.6 LB/EACH (11.6 KG/EACH)

NOTES:


- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- CAN BE USED WITH ANY INDUSTRY STANDARD 19" COMPONENTS IN ADDITION TO ALL PANDUIT CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
- WILL HOLD UP TO 42 SINGLE RACK SPACINGS.
- EIA SPACING ON RACK: I.E., REF. HOLE SPACING ON UPRIGHT CHANNELS: .625, .625, .500, .625, .625, .500, ETC.
- ASSEMBLY IS REQUIRED.
- RACK PART THICKNESSES:
 - UPRIGHT CHANNEL: WEB; .14 ±.03
FLANGE; .19 ±.03
 - TOP BRACKET: .187 ±.03
 - BASE BRACKET: .25 ±.03
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.
- ALL ASSEMBLY HARDWARE INCLUDED:
 - (12) 3/8-16 X 1" BLACK HEX HEAD CAP SCREW
 - (24) 3/8" PAINT PIERCING GROUNDING WASHER
 - (1) TUBE OF ANTI-OXIDIZING PASTE
 - (12) 3/8-16 BLACK HEX NUTS
 - (24) 12-24 X .5" SLOTTED PAN HEAD STEEL SCREWS
- LOAD RATING - 1000 LBS



CLOSE UP OF
VERTICAL CHANNEL

RU SPACINGS PRINTED
NUMBERING UP FROM
BOTTOM OF RACK

02A	11-14-13	BAME	PM	CMK	SEE SHEET 1 OF 2 FOR REVISIONS	V10687AK-DC
01A	6-22-10	BAME		CMK	SEE SHEET 1 OF 2 FOR REVISIONS	V10687AK-DC
00A	2-5-10	BAME	DPN	CMK	SEE SHEET 1 OF 2 FOR REVISIONS	V10687AK-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
6.5 FOOT CABLE MANAGEMENT RACK (R2P79)					
CUSTOMER DRAWING					
ITEM REVISION NAME			V10687AK/02		
DATASET FILE NAME			V10687AK_DC/02A		
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)</p> <p>.X ± .XXX ± .XX ± ANGLES ±</p> <p> THIRD ANGLE PROJECTION</p>			MATERIAL:		
			ALUMINUM		
			DRAWING NUMBER:		
			V10687AK - DC		
DRAWN BY	DATE	CHK	SCALE	SIZE	
BAME	2-5-10	DPN	NONE	SHT 2 OF 2	A