


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. FACTORY SETTINGS:
  - FRONT FACE OF FRONT E-RAILS ARE 167mm [6.57in] FROM FRONT FACE OF FRAME.
  - FRONT FACE OF REAR E-RAILS ARE 412.75mm [16.25in] FROM FRONT FACE OF FRONT E-RAILS.
4. ADJUSTMENTS:
  - RAIL ADJUSTMENT MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL.
  - FRONT E-RAILS CAN ADJUST AS FAR FORWARD AS 167mm [6.57in] FROM FRONT FACE OF FRAME.
  - WHEN FRONT E-RAILS ARE 167mm [6.57in] FROM FRONT FACE OF FRAME, REAR E-RAILS CAN ADJUST FROM 62mm [2.44in] TO 423mm [16.65in] AND FROM 473mm [18.62in] TO 975mm [38.38in].
5. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
6. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS  
15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in]...ETC.
7. PARTS SUPPLIED:
  - BASE CABINET
  - FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
  - REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
  - SPLIT SIDE PANELS (SEE CHART ON SHEET 2)
  - CAGE NUT UTILITY STYLE EQUIPMENT RAILS FRONT AND REAR (SEE CHART ON SHEET 2)
  - CABLE MANAGEMENT FINGERS (SEE CHART ON SHEET 2)
  - CABINET HARDWARE KIT
  - INSTRUCTION SHEET
8. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
9. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
10. STATIC LOAD RATING. 1360 Kg (3000 LBS)
11. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
12. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
13. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.

01A	11-20-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00A	7-09-14	PBS	ROJC	TCN	RELEASED TO PRODUCTION	12V352CN-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		NET-ACCESS S TYPE UTILITY CABINET - NO CASTERS 700mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING					
ITEM REVISION NAME		12V352CN/01.PRT					
DATASET FILE NAME		12V352CN_DC/01A.PRT					
		MATERIAL:					
		N/A					
		DRAWING NUMBER:					
		12V352CN-DC					
DRAWN BY		DATE	CHK	SCALE	THIRD ANGLE PROJECTION		
PBS		7-09-14	ROJC	NONE	SHT 1 OF 5		
					SIZE		
					A		



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	ADJUSTABLE FRONT UTILITY E-RAILS	REAR CAGE NUT FINGER MGMT E-RAILS	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS SET	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S7222*A9	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	00	01	135 Kg/EACH 297 LBS/EACH	155 Kg/EACH 342 LBS/EACH
S7522*A9	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	00	01	142 Kg/EACH 312 LBS/EACH	162 Kg/EACH 357 LBS/EACH
S7822*A9	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	00	01	148 Kg/EACH 327 LBS/EACH	169 Kg/EACH 372 LBS/EACH
S7229*A9	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	00	01	95 Kg/EACH 209 LBS/EACH	115 Kg/EACH 254 LBS/EACH
S7529*A9	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	00	01	102 Kg/EACH 225 LBS/EACH	122 Kg/EACH 270 LBS/EACH
S7829*A9	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	00	01	109 Kg/EACH 240 LBS/EACH	129 Kg/EACH 285 LBS/EACH

\* DENOTES COLOR

"B" = BLACK


"W" = WHITE

							TITLE NET-ACCESS S TYPE UTILITY CABINET - NO CASTERS 700mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352CN/01.PRT					
							DATASET FILE NAME 12V352CN_DC/01A.PRT					
01A	11-20-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				MATERIAL:  N/A	
00A	7-09-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CN-DC					DRAWING NUMBER: 12V352CN-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 7-09-14	CHK ROJC	SCALE NONE	SHT 2 OF 5	SIZE A

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



A


A

							TITLE NET-ACCESS S TYPE UTILITY CABINET - NO CASTERS 700mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352CN/01.PRT					
							DATASET FILE NAME 12V352CN_DC/01A.PRT					
											MATERIAL:  N/A	
01A	11-20-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 12V352CN-DC	
00A	7-09-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CN-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 7-09-14	CHK ROJC	SCALE NONE	SHT 3 OF 5	SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT DOOR, REAR DOOR,  
AND SIDE PANELS NOT SHOWN

(9) LOCATIONS  
TAPPED FOR M10  
THREADED ROD

REAR

(2) 165mm X 165mm  
[6.5in] [6.5in]  
KNOCKOUTS FOR PDU  
POWER CORDS  
COMPATIBLE  
W/COOL BOOT  
P/N: CTGN6X6



FRONT


TOP VIEW

(14) CABLE  
OPENINGS  
(83mm X 120mm)  
[3.26in] [4.7in]  
WITH BEZELS  
AND COVERS  
COMPATIBLE  
W/ COOL BOOT  
P/N: CTGN3X5


01A	11-20-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	7-09-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CN-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE NET-ACCESS S TYPE UTILITY CABINET - NO CASTERS 700mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING	
ITEM REVISION NAME 12V352CN/01.PRT	<b>PANDUIT</b>
DATASET FILE NAME 12V352CN_DC/01A.PRT	
MATERIAL:  N/A	DRAWING NUMBER: 12V352CN-DC
THIRD ANGLE PROJECTION	
DRAWN BY PBS	DATE 7-09-14
CHK ROJC	SCALE NONE
SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



REAR OF CABINET  
BOTTOM VIEW

TITLE				NET-ACCESS S TYPE UTILITY CABINET - NO CASTERS 700mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING			
ITEM REVISION NAME				12V352CN/01.PRT			
DATASET FILE NAME				12V352CN_DC/01A.PRT			
 THIRD ANGLE PROJECTION				MATERIAL:			
				N/A			
				DRAWING NUMBER:			
				12V352CN-DC			
DRAWN BY		DATE		CHK		SCALE	
PBS		7-09-14		ROJC		NONE	
				SHT 5 OF 5		SIZE	
						A	

01A	11-20-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	
00A	7-09-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CN-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	