

Fire Alarm Non-Shielded Non-Plenum

Product Description

- PVC
- Solid conductor
- FPLR, UL Listed



Applications

- For Use With All Power Limited Circuits In Fire Protective Signaling

Specification

- CONDUCTOR: Solid bare copper
- INSULATION: PVC
- JACKET: PVC with rip cord
- STANDARDS: NEC FPLR, UL Listed
- TEMPERATURE: 75°C

Power limited fire alarm and communications cable for riser or nonriser applications. Fire alarm, smoke detectors, signaling and fire-protective circuits. Call your local sales representative for specific requirements.

<u>Part No.</u>	<u>Conductor Size AWG</u>	<u>No. of Conductors</u>	<u>Rating</u>	<u>Insulation</u>	<u>Insulation Thickness (in.)</u>	<u>Overall Jacket Thickness (in.)</u>	<u>Nom. O.D. (in.)</u>	<u>Approx. Wt. lb./1,000 ft.</u>
FA-1202C-1-1N-03	12	2	FPLR	PVC	0.012	0.015	0.264	62
FA-1204C-1-1N-03	12	4	FPLR	PVC	0.012	0.015	0.258	80
FA-1402C-1-1N-03	14	2	FPLR	PVC	0.010	0.015	0.212	40
FA-1404C-1-1N-03	14	4	FPLR	PVC	0.010	0.015	0.252	73
FA-1602C-1-1N-03	16	2	FPLR	PVC	0.010	0.015	0.183	28
FA-1604C-1-1N-03	16	4	FPLR	PVC	0.010	0.015	0.216	49
FA-1802C-1-1N-03	18	2	FPLR	PVC	0.010	0.015	0.156	19
FA-1804C-1-1N-03	18	4	FPLR	PVC	0.010	0.015	0.181	33
FA-1806C-1-1N-03	18	6	FPLR	PVC	0.010	0.015	0.223	49
FA-2204C-1-1N-03	22	4	FPLR	PVC	0.010	0.015	0.122	15

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.