





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENTS MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 141mm [5.5in] TO 532mm [20.9in] AND FROM 583mm [22.9in] TO 1085mm [42.7in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
15.88mm [.625in], 15.88mm [.625in],
12.70mm [.5in], 15.88mm [.625in],
15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
-BASE CABINET
-FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
-REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
-SPLIT SIDE PANELS (SEE SHEET 2)
-EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)
-PDU BRACKETS (SEE CHART ON SHEET 2)
-CASTERS (SEE CHART ON SHEET 2)
-CABINET HARDWARE KIT
-INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 1111mm [43.75].

01A	12-02-14	MDCA	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00A	4-10-13	MDCA	JDW	JDWE	RELEASED TO PRODUCTION	12V352AY-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM 800mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING				
ITEM REVISION NAME 12V352AY/01.PRT				
DATASET FILE NAME 12V352AY_DC/01A.PRT				
 THIRD ANGLE PROJECTION			MATERIAL: N/A	
			DRAWING NUMBER: 12V352AY-DC	
DRAWN BY MDCA	DATE 4-10-13	CHK	SCALE NONE	SHT 1 OF 5
				SIZE A



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S8222*T	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	164 Kg/EACH 363 LBS/EACH	185 Kg/EACH 408 LBS/EACH
S8522*T	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	171 Kg/EACH 378 LBS/EACH	191 Kg/EACH 423 LBS/EACH
S8822*T	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	02	02	02	00	02	04	00	00	178 Kg/EACH 393 LBS/EACH	198 Kg/EACH 438 LBS/EACH
S8229*T	NET-ACCESS S-TYPE CABINET 800mm X 42RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	125 Kg/EACH 276 LBS/EACH	145 Kg/EACH 321 LBS/EACH
S8529*T	NET-ACCESS S-TYPE CABINET 800mm X 45RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	132 Kg/EACH 291 LBS/EACH	152 Kg/EACH 336 LBS/EACH
S8829*T	NET-ACCESS S-TYPE CABINET 800mm X 48RU X 1200mm DEEP	01	01	00	02	02	00	02	04	00	00	138 Kg/EACH 306 LBS/EACH	159 Kg/EACH 351 LBS/EACH

* DENOTES COLOR

"B" = BLACK


"W" = WHITE


							TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM 800mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING						
							ITEM REVISION NAME 12V352AY/01.PRT						
							DATASET FILE NAME 12V352AY_DC/01A.PRT						
							 THIRD ANGLE PROJECTION					MATERIAL: N/A	
01A	12-02-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX						DRAWING NUMBER: 12V352AY-DC	
00A	4-10-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352AY-DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MDCA	DATE 4-10-13	CHK	SCALE NONE	SHT 2 OF 5	SIZE A	

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




							TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM 800mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING				<div>PANDUIT</div>	
							ITEM REVISION NAME 12V352AY/01.PRT					
							DATASET FILE NAME 12V352AY_DC/01A.PRT					
											MATERIAL: N/A	
01A	12-02-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	<div>THIRD ANGLE PROJECTION</div>				DRAWING NUMBER: 12V352AY-DC	
00A	4-10-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352AY-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MDCA	DATE 4-10-13	CHK	SCALE NONE	SHT 3 OF 5	SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




01A	12-02-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	4-10-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352AY-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM 800mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING	
ITEM REVISION NAME 12V352AY/01.PRT	PANDUIT
DATASET FILE NAME 12V352AY_DC/01A.PRT	
MATERIAL: N/A	DRAWING NUMBER: 12V352AY-DC
THIRD ANGLE PROJECTION	
DRAWN BY MDCA	DATE 4-10-13
CHK	SCALE NONE
SHT 4 OF 5	SIZE A


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



01A	12-02-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	4-10-13	MDCA	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V352AY-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM 800mm WIDE X 1200mm DEEP FAMILY CUSTOMER DRAWING				
ITEM REVISION NAME 12V352AY/01.PRT		PANDUIT		
DATASET FILE NAME 12V352AY_DC/01A.PRT				
 THIRD ANGLE PROJECTION		MATERIAL: N/A		
		DRAWING NUMBER: 12V352AY-DC		
DRAWN BY MDCA	DATE 4-10-13	CHK	SCALE NONE	SHT 5 OF 5
				A

2

1