

170-03077



Article Number: 170-03077

Expandable Braided Sleeving, 0.5" Dia., Orange, 500.0 ft/Bulk Reel

RoHS

Download drawing

Download spec sheet

Base Data

Local Order Number	170-03077
Type	BSP123B
Color	Orange (OG)
Features and Benefits	• Weave construction adjusts to twisting and flexing without creating wrinkles or bends. • Durable construction offers excellent abrasion and cut-through resistance as well as inertness to most chemicals and fungus. • Color options available to provide easy visual and safety identification of critical wiring components. • Expands to 150% of nominal diameter for fast, easy installation.
Product Description	General purpose expandable braided sleeving provides flexible abrasion protection for wire bundles and hoses.
Short Description	Expandable Braided Sleeving, 0.5" Dia., Orange, 500.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	500.0 ft
Length L (Metric)	152.4 m
Reel Length (imperial)	500.0 ft
Bundle Diameter Min. (Imperial)	0.25 "
Bundle Diameter Min. (Metric)	6.4 mm
Bundle Diameter Max. (Imperial)	0.75 "
Bundle Diameter Max. (Metric)	19.1 mm
Nominal Diameter (Imperial)	1/2 "
Nominal Diameter (Metric)	12.7 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	500 ft
Package Quantity (Metric)	500.0 ft
Weight (Metric)	1.75 kg
Weight (imperial)	3.9

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Flammability	FMVSS 302 UL94 V0 FAR 25

Halogenfree Yes

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes