




760037218 | P-024-OD-8W-FSUBK
Indoor/Outdoor Plenum Distribution Cable, 24 fiber single-unit

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Total Fiber Count	24
Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Fiber Type, quantity	24
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Cable Weight	42.0 lb/kft 62.0 kg/km
Diameter Over Jacket	7.90 mm 0.31 in

Physical Specifications

Minimum Bend Radius, loaded	11.9 cm 4.7 in
Minimum Bend Radius, unloaded	7.9 cm 3.1 in
Tensile Load, long term, maximum	90 lbf 400 N
Tensile Load, short term, maximum	300 lbf 1335 N
Vertical Rise, maximum	500.0 m 1640.4 ft

760037218 | P024-OD-8W-FSUBK

Flame Test Specifications

Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	126 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	4.34 ft lb 5.88 N-m
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze Test Method	IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-40 °C to +70 °C (-40 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696 Telcordia GR-20 (water penetration) Telcordia GR-409
-------------------------------	--

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



760037218 | P024-OD-8W-FSUBK

Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable