

TAG61L-788

Article Number: 594-61788

Laser Tag Label, 1.0" X 2.625", 30 Per Sheet, Polyester, White, 7500/pkg



 Download spec sheet

Base Data

Local Order Number	TAG61L-788
Type	TAG61L
Color	White (WH)
Features and Benefits	• LaserTags are sheet fed for easy loading and fast printing. • LaserTags are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing. • LaserTags are printable using toner for long term UV exposure. • LaserTags come in a variety of label sizes and types to fit most applications.
Product Description	LaserTags are durable, laser printable labels for applications requiring clear, crisp legibility. The labels are supplied on 8.5" X 11" sheets and are printable using HellemannTyton Tagprint Pro software and a standard laser printer. Specially designed adhesives and materials are used for the LaserTags, ensuring that the labels will not curl, change color, or jam standard laser printers.
Short Description	Laser Tag Label, 1.0" X 2.625", 30 Per Sheet, Polyester, White, 7500/pkg

Product Dimensions

Length L (Imperial)	1.0 "
Length L (Metric)	25.4 mm
Width W (Imperial)	2.62 "
Width W (Metric)	66.67 mm
Height H (Imperial)	1.0 "
Height H (Metric)	25.4 mm
Height of printable area (imperial)	1.0 "
Height of printable area (metric)	25.4 mm
Horizontal Repeat HR (imperial)	2.620 "
Horizontal Repeat HR (metric)	66.67 mm
Print Method	Laser
Thickness T (Metric)	64.0 µm
Vertical Repeat VR (metric)	25.40 mm
Vertical Repeat VR (imperial)	1.0 "

Logistics and Packaging

Quantity Per	pack
Package Quantity	7500
Package Quantity (Metric)	7500
Carton Quantity	7500

Labels per Column 10

Labels per Row 3

Labels per Sheet 30

Material and Specifications

Material Type 788, Polyethylenterephthalat (PET)

Material Shortcut 788

Adhesive Acrylic

Adhesive Shortcut Acrylic

Operating Temperature -40°F to +199°F (-40°C to +93°C)

ROHS Compliant Yes