

Product information

SPIDER III - SPIDER-PL-20-06T1Z6Z6Z6TZ9HHHH

Industrial Ethernet:Unmanaged Industrial Ethernet Switches:SPIDER III-Switches:SPIDER III

<https://www.e-catalog.beldensolutions.com:443/link/57078-24455-49855-437329-458868/en/SPIDER-PL-20-06T1Z6Z6Z6TZ9HHHH/ui/state>

Name		SPIDER III
		
		Unmanaged, Industrial ETHERNET Rail Switch, fanless design, store and forward switching mode, 10/100 Mbit/s Ethernet
Delivery informations		
Availability		available
Product description		
Description		Unmanaged, Industrial ETHERNET Rail Switch, fanless design, store and forward switching mode, 10/100 Mbit/s Ethernet
Port type and quantity		6x 10/100BASE-TX, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity, 3 x 100Mbit/s SFP
Type		SPIDER-PL-20-06T1Z6Z6Z6TZ9HHHH
Order No.		942141027
More Interfaces		
Power supply/signaling contact		1 x plug-in terminal block, 6-pin
Network size - length of cable		
Twisted pair (TP)		0 m ... 100 m
Multimode fiber (MM) 50/125 µm		0 - 5000 m, 0 - 8 dB link budget (with M-FAST SFP-MM/LC)
Multimode fiber (MM) 62.5/125 µm		0 - 4000 m, 0 - 11 dB link budget (with M-FAST SFP-MM/LC)
Single mode fiber (SM) 9/125 µm		0 - 25 km, 0 - 13 dB link budget (with M-FAST SFP-SM/LC)
Network size - cascading		
Line - / star topology		any
Power requirements		
Operating voltage		12/24 V DC (9.6 - 32 V DC), redundant
Current consumption at 24 V DC		Max. 350 mA
Power consumption		Max. 9.0 W, 30.7 Btu (IT) h
Ambient conditions		
Operating temperature		-40 °C ... 70 °C
Storage/transport temperature		-40 °C ... 85 °C
Relative humidity (non-condensing)		0 % ... 95 %
Mechanical construction		
Dimensions (W x H x D)		56 x 135 x 117 mm (w/o terminal block)
Mounting		DIN Rail
Weight		510 g
Protection class		IP40 metal housing
Mechanical stability		
IEC 60068-2-27 shock		15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration		3.5 mm, 5-8.4 Hz, 10 cycles, 1 octave/min; 1 g, 8.4-150 Hz, 10 cycles, 1 octave/min
Configurable parameters		
Configurable parameters		Global settings: power supply unit alarm, aging time, QoS 802.1p mapping, QoS DSCP mapping; Port settings: flow control, port admin state, broadcast storm protection/threshold, multicast storm protection/threshold, QoS Trust Mode, port based priority, link alarm; TX port settings: auto-negotiation, speed, duplex mode, auto-crossing, MDI state, energy efficient ethernet; FX port settings: duplex mode
EMC interference immunity		
EN 61000-4-2 electrostatic discharge (ESD)		4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field		10 V/m (80-1000 MHz)
EN 61000-4-4 fast transients (burst)		2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage		power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity		10 V (150 kHz-80 MHz)
EMC emitted immunity		
FCC CFR47 Part 15		FCC 47 CFR Part 15 Class A

Industrial Ethernet:Unmanaged Industrial Ethernet Switches:SPIDER III-Switches:SPIDER III
<https://www.e-catalog.beldensolutions.com:443/link/57078-24455-49855-437329-458868/en/SPIDER-PL-20-06T1Z6Z6TZ9HHHH/uistate>

EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	UL61010-1/-2-201 (pending)
Scope of delivery and accessories	
Scope of delivery	Device, terminal block, safety instruction
Accessories	Rail Power Supply RPS 30/80 EEC/120 EEC (CC), Wall mounting plate for DIN rail mounting (width 40/70 mm)

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.