



SAFETY DATA SHEET ARBOSIL 1090

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name ARBOSIL 1090

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Neutral cure building sealant.

1.3. Details of the supplier of the safety data sheet

Supplier Adshead Ratcliffe & Co. Ltd.
Derby Road, Belper
Derbyshire.
DE56 1WJ
Tel. (+44) 01773 826661
Fax. (+44) 01773 821215
sds@arbo.co.uk

1.4. Emergency telephone number

Emergency telephone (+44) 01773 826661 (office hours only)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification

Physical hazards Not Classified
Health hazards Eye Dam. 1 - H318
Environmental hazards Not Classified

2.2. Label elements

Pictogram



Signal word Danger

Hazard statements H318 Causes serious eye damage.

Precautionary statements P280 Wear eye protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 If eye irritation persists: Get medical advice/attention.

Contains TITANIUMACETYLACETATE

2.3. Other hazards

SECTION 3: Composition/information on ingredients

ARBOSIL 1090

3.2. Mixtures

TITANIUMACETYLACETATE		1-5%
CAS number: 83877-91-2	EC number: 281-161-6	
Classification Flam. Liq. 3 - H226 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT SE 3 - H335, H336		
BIS-(N-METHYLBENZAMIDO)-METHYLETHOXSILANE		1-5%
CAS number: 16230-35-6	EC number: 240-354-5	
Classification Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 STOT SE 3 - H335		
n-METHYLBENZAMID		<1%
CAS number: 613-93-4	EC number: 210-362-3	
Classification Acute Tox. 3 - H301 Eye Irrit. 2 - H319		
DIOCTYLTIN DILAURATE		<1%
CAS number: 3648-18-8	EC number: 222-883-3	
Classification Repr. 2 - H361 STOT RE 2 - H373		

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	In all cases of doubt, or if symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.
Inhalation	If inhalation causes adverse effects, remove to fresh air.
Ingestion	Rinse mouth thoroughly with water. Give plenty of water to drink. Give milk instead of water if readily available. Do not induce vomiting. Get medical attention if any discomfort continues.
Skin contact	Wipe off excess material with cloth or paper. Wash skin thoroughly with soap and water. Get medical attention if any discomfort continues.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	No specific symptoms known.
-------------------	-----------------------------

ARBOSIL 1090

Ingestion	May cause discomfort if swallowed.
Skin contact	Skin irritation should not occur when used as recommended.
Eye contact	May cause serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Water spray, fog or mist. Foam, carbon dioxide or dry powder.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	No unusual fire or explosion hazards noted.
Hazardous combustion products	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	No specific firefighting precautions known.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Wear appropriate protective clothing. Avoid contact with eyes.
----------------------	--

6.2. Environmental precautions

Environmental precautions	Do not discharge into drains or watercourses or onto the ground.
---------------------------	--

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	Collect and place in suitable waste disposal containers and seal securely. Clean any slippery coating that remains using a detergent / soap solution or other biodegradable cleaner.
-------------------------	--

6.4. Reference to other sections

Reference to other sections	For personal protection, see Section 8. See Section 11 for additional information on health hazards. For waste disposal, see section 13.
-----------------------------	--

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions	Avoid spilling. Avoid contact with skin and eyes.
Advice on general occupational hygiene	Good personal hygiene procedures should be implemented. Wash hands thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions	Store in tightly-closed, original container in a dry, cool and well-ventilated place.
Storage class	Unspecified storage.

7.3. Specific end use(s)

ARBOSIL 1090

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

Usage description Gunnable sealant.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

DIOCTYL TIN DILAURATE

Long-term exposure limit (8-hour TWA): WEL 0.1 mg/m³

Short-term exposure limit (15-minute): WEL 0.2 mg/m³

as Sn

WEL = Workplace Exposure Limit

TITANIUM ACETYLACETATE (CAS: 83877-91-2)

DNEL

Workers - Inhalation; Long term systemic effects: 254 mg/m³

General population - Inhalation; Long term systemic effects: 303 mg/m³

General population - Dermal; Long term systemic effects: 220 mg/kg/day

General population - Oral; Long term systemic effects: 22 mg/kg/day

PNEC

- Fresh water; 0.1 mg/l

- Marine water; 0.01 mg/l

- Intermittent release; 1 mg/l

- STP; 28 mg/l

- Sediment (Freshwater); 0.0816 mg/kg

- Sediment (Marinewater); 0.0082 mg/kg

- Soil; 0.019 mg/kg

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Wear eye protection. Personal protective equipment for eye and face protection should comply with European Standard EN166.

Hand protection

Wear protective gloves. The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with European Standard EN374.

Other skin and body protection

Provide eyewash station.

Hygiene measures

Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap and water if skin becomes contaminated.

Respiratory protection

No specific recommendations.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

ARBOSIL 1090

Appearance	Uncured -paste. Cured - rubber.
Colour	Various colours.
Odour	Slight.
Odour threshold	Not applicable.
pH	Not applicable.
Melting point	Not applicable.
Initial boiling point and range	Not applicable.
Flash point	Not applicable.
Evaporation rate	Not applicable.
Evaporation factor	Not applicable.
Upper/lower flammability or explosive limits	Not applicable.
Vapour pressure	Not applicable.
Vapour density	Not applicable.
Relative density	1.18 - 1.20 @ 20°C
Solubility(ies)	Insoluble in water.
Partition coefficient	Not applicable.
Auto-ignition temperature	As paste: 450°C
Decomposition Temperature	Not determined.
Viscosity	5,000 - 7,000 P @ 20°C
Explosive properties	Not applicable.
Oxidising properties	The mixture itself has not been tested but none of the ingredient substances meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid Avoid excessive heat for prolonged periods of time.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

ARBOSIL 1090

10.6. Hazardous decomposition products

Hazardous decomposition products	None at ambient temperatures. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.
---	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects	There are no data available on this product.
<u>Acute toxicity - oral</u>	
ATE oral (mg/kg)	22,433.04
<u>Acute toxicity - dermal</u>	
Notes (dermal LD₅₀)	For this endpoint no toxicological data is available for the whole product.
<u>Acute toxicity - inhalation</u>	
Notes (inhalation LC₅₀)	For this endpoint no toxicological data is available for the whole product.
<u>Skin corrosion/irritation</u>	
Animal data	Based on available data the classification criteria are not met.
<u>Serious eye damage/irritation</u>	
Serious eye damage/irritation	Contains a substance which is classified as causing serious damage to eyes.
<u>Skin sensitisation</u>	
Skin sensitisation	Based on available data the classification criteria are not met.
<u>Germ cell mutagenicity</u>	
Genotoxicity - in vitro	Based on available data the classification criteria are not met.
<u>Carcinogenicity</u>	
Carcinogenicity	Based on available data the classification criteria are not met.
<u>Reproductive toxicity</u>	
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Aspiration hazard	Not relevant, due to the form of the product.
<u>Inhalation</u>	
Inhalation	Not relevant at normal room temperatures. When heated, toxic vapours may be formed.
<u>Ingestion</u>	
Ingestion	May cause discomfort if swallowed.
<u>Skin contact</u>	
Skin contact	Prolonged skin contact may cause temporary irritation.
<u>Eye contact</u>	
Eye contact	May cause serious eye damage.

Toxicological information on ingredients.

TITANIUMACETYLACETATE

Acute toxicity - oral

ARBOSIL 1090

Notes (oral LD₅₀) LD₅₀ > 2000 mg/kg, Oral, Rat

Acute toxicity - inhalation

Notes (inhalation LC₅₀) LC₅₀ 18180 mg/m³, Inhalation, Rat Read-across data.

SECTION 12: Ecological Information

Ecotoxicity In cross-linked state not soluble in water. Easily separable from water by filtration.

12.1. Toxicity

Toxicity There are no data for the product.

Ecological information on ingredients.

TITANIUMACETYLACETATE

Acute toxicity - fish LC₅₀, 96 hours: 1460 mg/l, Pimephales promelas (Fat-head Minnow)

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: >= 100 mg/l, Daphnia magna

Acute toxicity - aquatic plants EC₅₀, 72 hours: > 100 mg/l, Pseudokirchneriella subcapitata

Acute toxicity - microorganisms TT (Toxicity threshold), 16 hours: 280 mg/l, Pseudomonas putida

12.2. Persistence and degradability

Persistence and degradability Silicone content: biologically not degradable.

Ecological information on ingredients.

TITANIUMACETYLACETATE

Biodegradation Expected to be readily biodegradable.
Water - Degradation 44%: 23 hours
Read-across data.

12.3. Bioaccumulative potential

Bioaccumulative potential Bioaccumulation is unlikely to be significant because of the low water-solubility of this product.

Partition coefficient Not applicable.

12.4. Mobility in soil

Mobility The product is insoluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Confirm disposal procedures with environmental engineer and local regulations.

ARBOSIL 1090

Waste class Not hazardous by HP4: ingredients classified as H318 <10% Recommended EWC Code 08 04 10

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78

and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation Regulation (EC) 1907/2006 REACH (as amended).
Regulation (EC) 1272/2008 CLP (as amended).

Guidance Workplace Exposure Limits EH40.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments Classification and labelling according to CLP Regulations.

Revision date 17/09/2015

Supersedes date 14/11/2012

SDS number 10165

ARBOSIL 1090

Hazard statements in full

H226 Flammable liquid and vapour.
H301 Toxic if swallowed.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.
H336 May cause drowsiness or dizziness.
H361 Suspected of damaging fertility or the unborn child.
H373 May cause damage to organs through prolonged or repeated exposure.