



SAFETY DATA SHEET ARBOSIL LM - Colours

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name ARBOSIL LM - Colours

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Supplier Adshead Ratcliffe & Co. Ltd.
Derby Road, Belper
Derbyshire.
DE56 1WJ
Tel. (+44) 01773 826661
Fax. (+44) 01773 821215
sds@arbo.co.uk

1.4. Emergency telephone number

Emergency telephone (+44) 01773 826661 (office hours only)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification

Physical hazards Not Classified
Health hazards Skin Sens. 1 - H317
Environmental hazards Not Classified

2.2. Label elements

Pictogram



Signal word Warning
Hazard statements H317 May cause an allergic skin reaction.
Precautionary statements P280 Wear protective gloves.
Contains METHYL-0,0',0"-BUTAN-2-ONE-TRIOXIMOSILANE

2.3. Other hazards

SECTION 3: Composition/information on ingredients

3.2. Mixtures

ARBOSIL LM - Colours

METHYL-0,0',0"-BUTAN-2-ONE-TRIOXIMOSILANE		1-5%
CAS number: 22984-54-9	EC number: 245-366-4	
Classification		
Eye Irrit. 2 - H319		
Skin Sens. 1 - H317		
STOT RE 2 - H373		

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	In all cases of doubt, or if symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.
Inhalation	If inhalation causes adverse effects, remove to fresh air.
Ingestion	Rinse mouth thoroughly with water. Give plenty of water to drink. Give milk instead of water if readily available. Do not induce vomiting. Get medical attention if any discomfort continues.
Skin contact	Wipe off excess material with cloth or paper. Wash skin thoroughly with soap and water. Get medical attention promptly if symptoms occur after washing. In the event of any sensitisation symptoms developing, ensure further exposure is avoided.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	No specific symptoms known.
Ingestion	May cause discomfort if swallowed.
Skin contact	Allergic rash.
Eye contact	May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations.
-----------------------------	------------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Water spray, fog or mist. Foam, carbon dioxide or dry powder.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	No unusual fire or explosion hazards noted.
Hazardous combustion products	Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting	No specific firefighting precautions known.
---	---

ARBOSIL LM - Colours

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear appropriate protective clothing. Avoid contact with eyes and skin.

6.2. Environmental precautions

Environmental precautions Do not discharge into drains or watercourses or onto the ground.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Collect and place in suitable waste disposal containers and seal securely. Clean any slippery coating that remains using a detergent / soap solution or other biodegradable cleaner.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid spilling. Avoid contact with skin and eyes. Persons susceptible to allergic reactions should not handle this product. Good personal hygiene procedures should be implemented.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container in a dry, cool and well-ventilated place.

Storage class Unspecified storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

Usage description Gunnable sealant.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

Use protective gloves. The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material.

Hygiene measures

Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap and water if skin becomes contaminated.

Respiratory protection

No specific recommendations.

ARBOSIL LM - Colours

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Paste.
Colour	Various colours.
Odour	Slight.
Odour threshold	Not determined.
pH	pH (concentrated solution): Not applicable.
Melting point	Not applicable.
Initial boiling point and range	Not applicable.
Flash point	Not applicable.
Evaporation rate	Not applicable.
Evaporation factor	Not applicable.
Upper/lower flammability or explosive limits	Not applicable.
Vapour pressure	Not applicable.
Vapour density	Not applicable.
Relative density	1.28 @ 20C
Solubility(ies)	Insoluble in water.
Partition coefficient	Not applicable.
Auto-ignition temperature	Not applicable.
Decomposition Temperature	Not determined.
Viscosity	8000 - 10000 P @ 20°C
Explosive properties	Not applicable.
Oxidising properties	Not applicable.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
------------	---

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended. Moisture curing process releases: a small amount of butanone-2-oxime (MEKO)
-----------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not known. Will not polymerise.
------------------------------------	---------------------------------

10.4. Conditions to avoid

Conditions to avoid	Avoid excessive heat for prolonged periods of time.
---------------------	---

10.5. Incompatible materials

ARBOSIL LM - Colours

Materials to avoid Strong oxidising agents.

10.6. Hazardous decomposition products

Hazardous decomposition products Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours. Oxides of carbon. Oxides of nitrogen.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects Butanone-2-oxime (MEKO) is damaging to nasal membranes in rats and mice at a concentration in excess of 10ppm over a prolonged period of time.

Acute toxicity - oral

Notes (oral LD₅₀) For this endpoint no toxicological data is available for the whole product.

Acute toxicity - dermal

Notes (dermal LD₅₀) For this endpoint no toxicological data is available for the whole product.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) For this endpoint no toxicological data is available for the whole product.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation The product contains a small amount of a sensitising substance which may cause an allergic reaction in sensitive individuals.

Germ cell mutagenicity

Genotoxicity - in vitro Does not contain any substances known to be mutagenic.

Carcinogenicity

Carcinogenicity Does not contain any substances known to be carcinogenic.

Reproductive toxicity

Reproductive toxicity - fertility Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Not relevant, due to the form of the product.

Inhalation No specific symptoms known.

Ingestion May cause discomfort if swallowed.

Skin contact May cause sensitisation by skin contact.

Eye contact May cause irritation to eyes.

SECTION 12: Ecological Information

ARBOSIL LM - Colours

Ecotoxicity In cross-linked state not soluble in water. Easily separable from water by filtration.

12.1. Toxicity

Toxicity There are no data for the product.

12.2. Persistence and degradability

Persistence and degradability This product is not expected to be readily biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential Bioaccumulation is unlikely to be significant because of the low water-solubility of this product.

Partition coefficient Not applicable.

12.4. Mobility in soil

Mobility The product is insoluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Confirm disposal procedures with environmental engineer and local regulations.

Waste class Recommended EWC Code 08 04 09* HP13 Sensitising

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

No information required.

14.2. UN proper shipping name

No information required.

14.3. Transport hazard class(es)

No information required.

14.4. Packing group

No information required.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

No information required.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

ARBOSIL LM - Colours

Transport in bulk according to No information required.
Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation Regulation (EC) 1907/2006 REACH.
Regulation (EC) 1272/2008 CLP.

Guidance Workplace Exposure Limits EH40.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	Classification and labelling according to CLP Regulations.
Revision date	01/06/2015
Supersedes date	11/12/2013
SDS number	10136
Hazard statements in full	H317 May cause an allergic skin reaction. H319 Causes serious eye irritation. H373 May cause damage to organs (Blood) through prolonged or repeated exposure if swallowed.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.