


760127837 | P-048-DZ-8W-FMUYL
Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, 48 fiber multi-unit with 12 fiber subunits

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Total Fiber Count	48
Armor Type	Interlocking aluminum
Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1)
Fiber Type, quantity	48
Fibers per Subunit, quantity	12
Jacket Color	Yellow

Dimensions

Buffer Tube/Subunit Diameter	5.77 mm 0.23 in
Cable Weight	302.0 lb/kft 449.0 kg/km
Diameter Over Armor	20.96 mm 0.83 in
Diameter Over Jacket	23.00 mm 0.91 in
Subunit, quantity	4

Physical Specifications

Minimum Bend Radius, loaded	46.0 cm 18.1 in
Minimum Bend Radius, unloaded	32.2 cm 12.7 in

760127837 | P048-DZ-8W-FMUYL

Tensile Load, long term, maximum 400 N | 90 lbf
Tensile Load, short term, maximum 1335 N | 300 lbf
Vertical Rise, maximum 91.0 m | 298.6 ft

Flame Test Specifications

Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	485 lb/in 85 N/mm
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	25.80 ft lb 35.00 N-m
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596 Telcordia GR-409
-------------------------------	---------------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable