

This specification is OBSOLETE

CX3199914 | 0750135PP200ROPE COEX

ConQuest® Empty Conduit, 3/4 in, SDR 13.5, orange, with pull rope



OBSOLETE

This product was discontinued on: March 13, 2015

Dimensions

| | |
|----------------------------|-----------------------|
| Nominal Size | 3/4 in |
| Wall Thickness Designation | SDR 13.5 |
| Inner Diameter, nominal | 22.200 mm 0.874 in |
| Length | 304.80 m 1000.00 ft |
| Outer Diameter, nominal | 26.670 mm 1.050 in |
| Wall Thickness, minimum | 1.981 mm 0.078 in |
| Weight | 111.0 lb/kft |

General Specifications

| | |
|--------------|--------------|
| Color | Orange |
| Conduit Type | Non-toneable |
| Wall Type | Smooth |
| Brand | ConQuest® |
| Warranty | One year |

Material Specifications

| | |
|---------------------------------------|-------------------------------------|
| Density Test Method | ASTM D792A |
| Density, maximum | 0.955 g/cm ³ |
| Density, minimum | 0.941 g/cm ³ |
| Design Standard | ASTM D3350-05 |
| Environmental Stress Crack Resistance | Failure rate of 10% within 96 hours |
| Environmental Stress Test Method | ASTM D1693, ESCR Condition B |
| Flexural Modulus, minimum | 552 N/mm ² 80000 psi |
| Flexural Property Test Method | ASTM D790 |
| Hydrostatic Design Basis | Not pressure rated |
| Hydrostatic Design Test Method | ASTM D2837 |
| Material Type | High density polyethylene (HDPE) |
| Melt Flow Rate Test Method | ASTM D1238 |

CX3199914 | 075O135PP200ROPE COEX

| | |
|------------------------------------|---------------------------------|
| Melt Flow Rate, maximum | 0.39 g/10 min |
| Tensile Property Test Method | ASTM D638 |
| Tensile Strength at yield, minimum | 21 N/mm ² 3000 psi |

Mechanical Specifications

| | |
|----------------------------------|---------------------|
| Minimum Bend Radius, unsupported | 304.8 mm 12.0 in |
| Pulling Tension, maximum | 229.1 kg 505.0 lb |

Pull Line Specifications

| | |
|-------------------|--------------------|
| Breaking Strength | 90.7 kg 200.0 lb |
| Material Type | Polypropylene |
| Pull Line Type | Rope |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance