ProLabs

DATA SHEET: Transceivers

PROLABS - GP-SFP2-1S-C

1.25GBd SFP (Small Form Pluggable) Short Wavelength (850nm) Transceiver

GP-SFP2-1S-C Overview

PROLABS's GP-SFP2-1S-C SFP optical transceivers are based on Gigabit Ethernet IEEE 802.3 standard and Fiber Channel FC-PI Rev.5.0 and provide a quick and reliable interface for the GE/FC application. The Digital diagnostics functions are available via 2-wire serial bus specified in the SFP MSA. In addition, they comply with the Small Form Factor Pluggable Multi Sourcing Agreement (MSA) and SFF-8472.

Product Features

- Up to 1.25 GBd bi-directional data links
- Compliant with IEEE 802.3z Gigabit Ethernet and 1000BASE-SX
- Compliant with SFP MSA
- Hot-pluggable SFP footprint
- 850nm VCSEL laser transmitter
- Duplex LC connector
- Built-in digital diagnostic functions
- Up to 550m on 50/125um MMF
- Up to 300m on 62.5/125um MMF
- Single power supply 3.3V
- RoHS Compliance
- Class 1 laser product complies with EN 60825-1
- Operating temperature range: 0°C to 70°C.

Applications

- 1.25 GBd Gigabit Ethernet
- 1.063 GBd Fiber Channel

Ordering Information

Oracing information	VII
Part Number	Description
GP-SFP2-1S-C	GE/FC SFP 850nm LC Connectors 550m on MMF, with DOM function.

General Specifications

Parameter	Symbol	Min	Тур	Мах	Unit	Remarks
Deta Deta	, DD		1.25		CD4	IEEE 802.3
Data Rate	DR		1.062		GBd	FC-PI-2 Rev 5
Bit Error Rate	BER			10^{-12}		
Operating Temperature	T_{OP}	0		70	°C	Case temperature
Storage Temperature	T_{STO}	- 40		85	°C	Ambient temperature
Supply Current	I _S		180	240	mA	For electrical power interface
Input Voltage	V_{CC}	3	3.3	3.6	V	
Maximum Voltage	V_{MAX}	- 0.5	•	4	V	For electrical power interface



Optical Characteristics – Transmitter $V_{CC}=3V$ to 3.6V, $T_{C}=0$ °C to 70°C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Output Optical Power						
50/125um fiber, NA=0.2	P_{TX}	- 9		– 3	dBm	Class 1 Product
62.5/125um fiber, NA-0.275						
Optical Center Wavelength	$\lambda_{\mathbf{C}}$	830		860	nm	
Optical Modulation Amplitude@1.063GBd	OMA	156			uW	Equivalent extinction ratio specification for FC
Extinction Ratio@1.25GBd	ER	9			dB	
Spectral Width (RMS)	$\Delta\lambda$			0.85	nm	
Optical Rise/Fall Time (20% - 80%)	T_{RF_IN}		100	150	ps	
Relative Intensity Noise	RIN			- 120	dB/Hz	
Deterministic Jitter Contribution	TX_∆DJ		20	60	ps	
Total Jitter Contribution	TX_∆TJ		65	125	ps	
Mask Margin			45%			

Optical Characteristics – Receiver V_{cc} =3V to 3.6V, T_c =0 $^{\circ}$ C to 70 $^{\circ}$ C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Optical Receiver Power	P_{RX}			0	dBm	Average
Optical Center Wavelength	λ_{C}	770		860	nm	
Receiver Sensitivity @ 1.063GBd	R _{X_SEN1}			- 20	dBm	FC-PI-2 Rev.5
Receiver Sensitivity @ 1.25GBd	R _{X_SEN2}			- 20	dBm	IEEE 802.3
Optical Return Loss	ORL	12			dB	
Receiver Electrical 3dB Upper cutoff				1500	MHz	
frequency				1500	IVII IZ	
Loss of Signal-Asserted	P_{LOS_A}	- 30			dBm	
Loss of Signal-Deasserted	P_{LOS_D}			- 20	dBm	
Loss of Signal-Hysteresis		0.5			dB	

Electrical Characteristics – Transmitter $V_{CC}=3V$ to 3.6V. $T_{C}=0$ °C to 70°C

166-01 10 010 1, 16-0 0 10 10 0						
Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Input differential impedance	R _{IN}		100		Ω	Non condensing
Single ended data input swing	V _{IN PP}	250		1200	mV	
Transmit disable voltage	V_D	2		V _{CC}	V	
Transmit enable voltage	V_{EN}	V_{EE}		V _{EE} +0.	V	
				Q		

Electrical Characteristics – Receiver $V_{CC}=3V$ to 3.6V, $T_{C}=0$ °C to 70°C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Single ended data output swing	V_{OUT_PP}	250	450	550	mV	
Data output rise time (20%-80%)	T_R		90	175	ps	
Data output fall time (20%-80%)	T_{F}		90	175	ps	
LOS Fault	V_{LOS_Fault}	2		V _{CC_HO}	V	
				ST		
LOS Normal	V_{LOS_normal}	V_{EE}		V_{EE} +0.	V	
				5		



Digital Diagnostic Functions

GP-SFP2-1S-C support the 2-wire serial communication protocol as defined in the SFP MSA. Digital diagnostic information are accessible over the 2-wire interface at the address 0xA2. Digital Diagnostics for GP-SFP2-1S-C are internally calibrated by default. A micro controller unit inside the transceiver gathers the monitoring information and reports the status of transceiver.

Transceiver Temperature, internally measured, represented as a 16 bit signed twos complement value in increments of 1/256 degrees Celsius, Temperature accuracy is better than ±3 degrees Celsius over specified operating temperature and voltage.

Transceiver Supply Power, internally measured, represented as a 16 bit unsigned integer with the voltage defined as the full 16 bit value (0-65535) with LSB equal to 100 μ Volt, yielding a total range of 0 to +6.55 Volts.


Transceiver TX bias current, internally measured, represented as a 16 bit unsigned integer with the current defined as the full 16 bit value (0 - 65535) with LSB equal to 2 μ A, yielding a total range of 0 to 131mA. Accuracy is better than $\pm 10\%$ over specified operating temperature and voltage.

Transceiver TX output power, internally measured, represented as a 16 bit unsigned integer with the power defined as the full 16 bit value (0 - 65535) with LSB equal to 0.1 μ W. Data is assumed to be based on measurement of laser monitor photodiode current. Accuracy is better than \pm 3dB over specified temperature and voltage. Data is not valid when the transmitter is disabled.

Transceiver RX received optical power, internally measured, represented as a 16 bit unsigned integer with the power defined as the full 16 bit 35 value (0-65535) with LSB equal to 0.1 μ W. Accuracy is better than ± 3 dB over specified temperature and voltage.

Parameter	Symbol	Accuracy	Units	Repor	t Range	Unit	Remarks
Temperature	T _{MON}	±3	°C	- 40	95	°C	
Voltage	V_{MON}	±0.1	V	2.7	3.9	V	
Bias Current	I _{MON}	±10	%	1	15	mA	
Tx Power	P _{MON}	±3	dB	- 12	1	dBm	
Rx Power	P _{MON}	±3	dB	- 25	1	dBm	

Block Diagram of Transceiver



Transmitter Section

The VCSEL driver accept differential input data and provide bias and modulation currents for driving a laser. An automatic power-control (APC) feedback loop is incorporated to maintain a constant average optical power. 850 nm VCSEL in an eye safe optical subassembly (OSA) mates to the fiber cable.

TX_DISABLE

The TX_DISABLE signal is high (TTL logic "1") to turn off the laser output. The laser will turn on within 1ms when TX_DISABLE is low (TTL logic "0").

TX_FAUL1

When the TX_FAULT signal is high, output indicates a laser fault of some kind. Low indicates normal operation.

Receiver Section

The receiver utilizes a PIN detector integrated with a trans-impedance preamplifier in an OSA. This OSA is connected to a Limiting Amplifier which providing post-amplification quantization, and optical signal detection. The limiting Amplifier is AC-coupled to the transimpedance amplifier, with internal 100Ω differential termination.

Receive Loss (RX_LOS)


The RX_LOS is high (logic "1") when there is no incoming light from the companion transceiver. This signal is normally used by the system for the diagnostic purpose. The signal is operated in TTL level.

Controller Section

The micro controller unit monitors the operation information of LD driver and Limiting Amplifier. And report these status to the customer.




Dimensions




ALL DIMENSIONS ARE ±0.2mm UNLESS OTHERWISE SPECIFIED UNIT: mm



PCB Layout Recommendation





- /Datum and Basic Dimension Established by Customer
- Rads and Vias are Chassis Ground, 11 Places
- AThrough Holes are Unplated






Electrical Pad Layout







Top of Board

Bottom of Board



Pin Assignment

PIN#	Symbol	Description	Remarks
1	V _{EET}	Transmitter ground (common with receiver ground)	Circuit ground is isolated from chassis ground
2	T_{FAULT}	Transmitter Fault. Not supported	<u> </u>
3	T_{DIS}	Transmitter Disable. Laser output disable on high or open	Disabled: T _{DIS} >2V or open Enabled: T _{DIS} <0.8V
4	MOD_DEF (2)	Module Definition 2. Data line for serial ID	Should Be pulled up with
5	MOD_DEF (1)	Module Definition 1. Clock line for serial ID	4.7k – 10k ohm on host
6	MOD_DEF (0)	Module Definition 0. Grounded within the module	board to a voltage between 2V and 3.6V
7	Rate Select	No connection required	
8	LOS	Loss of Signal indication. Logic 0 indicates normal operation	LOS is open collector output
9	V_{EER}	Receiver ground (common with transmitter ground)	Circuit around in
10	V_{EER}	Receiver ground (common with transmitter ground)	Circuit ground is isolated
11	V_{EER}	Receiver ground (common with transmitter ground)	from chassis ground
12	RD-	Receiver Inverted DATA out. AC coupled	
13	RD+	Receiver Non-inverted DATA out. AC coupled	
14	V_{EER}	Receiver ground (common with transmitter ground)	Circuit ground is isolated from chassis ground
15	V_{CCR}	Receiver power supply	
16	V_{CCT}	Transmitter power supply	
17	V_{EET}	Transmitter ground (common with receiver ground)	Circuit ground is connected to chassis ground
18	TD+	Transmitter Non-Inverted DATA in. AC coupled	
19	TD-	Transmitter Inverted DATA in. AC coupled	
20	V_{EET}	Transmitter ground (common with receiver ground)	Circuit ground is connected to chassis ground

References

- 1. IEEE standard 802.3. IEEE Standard Department, 2002.
- Small Form Factor Pluggable (SFP) Transceiver Multi-Source Agreement (MSA), September 2000.
 Fiber Channel Draft Physical Interface Specification (FC-PI-2 Rev.5).
 Digital Diagnostics Monitoring Interface for Optical Transceivers SFF-8472.