# PROLABS-QK724A-C

14.025GBd SFP+ Short Wavelength (850nm) Transceiver

### QK724A-C Overview

PROLABS's QK724A-C SFP+ optical transceivers are based on Fiber Channel Links up to 14.025Gb/s data rate over multimode fiber, and they are compliant with PC-PI-4 Rev 7.0 and SFF-8472 Rev 10.1 and compatible with SFF-8432 and applicable portions of SFF-8431 Rev 1.3.

#### **Product Features**

- Up to 14.025 GBd bi-directional data links
- Compliant with SFF 8431 & SFF 8432
- Hot-pluggable SFP+ footprint
- 850nm VCSEL laser transmitter
- Duplex LC connector
- Built-in digital diagnostic functions
- Up to 100m on OM3 MMF
- Single power supply 3.3V
- RoHS Compliance
- Class 1 laser product complies with EN 60825-1
- Operating temperature range: 0°C to 70°C.

#### **Applications**

- 4.25G Fiber Channel
- 8.25G Fiber Channel
- 14.025G Fiber Channel

## **Ordering Information**

Ordering information	
Part Number	Description
QK724A-C	14.025G SFP+ 850nm LC Connectors 100m on MMF, with DOM function.

**General Specifications** 

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Data Rate	DR		14.025		GBd	IEEE 802.3ae
Bit Error Rate	BER			$10^{-12}$		
Operating Temperature	$T_{OP}$	0		70	°C	Case temperature
Storage Temperature	$T_{STO}$	<b>- 40</b>		85	°C	Ambient temperature
Supply Current	I <sub>S</sub>		180	220	mA	For electrical power interface
Input Voltage	V <sub>CC</sub>	3	3.3	3.6	V	
Maximum Voltage	$V_{MAX}$	- 0.5		4	V	For electrical power interface



Optical Characteristics – Transmitter  $V_{CC}$ =3V to 3.6V,  $T_{C}$ =0C to 70C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Output Optical Power	$P_{TX}$	- 7.8		<b>– 1</b>	dBm	Class 1 Product
Optical Center Wavelength	$\lambda_{C}$	840	850	860	nm	
Extinction Ratio	ER	3.0	5.5		dB	
Spectral Width (RMS)	Δλ			0.65	nm	
Relative Intensity Noise	RIN			<b>- 128</b>	dB/Hz	
Transmitter Dispersion Penalty	TDP			4.3	dB	
Transmitter Jitter		Acc	cording to	<b>IEEE 802</b>	.3ae requ	irement
Launch Power of OFF Transmitter	$P_{OUT\_OFF}$			- 30	dBm	Average

Optical Characteristics – Receiver

 $V_{CC}$ =3V to 3.6V,  $T_{C}$ =0°C to 70°C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Optical Center Wavelength	$\lambda_{C}$	840	850	860	nm	
Receiver Sensitivity (OMA)@ 4.25G	R <sub>X_SEN1</sub>			<b>- 12</b>	dBm	Measured with a PRBS 2 <sub>7</sub> -1 test pattern @ 4.25Gbps, BER≤10- <sub>12</sub>
Receiver Sensitivity (OMA)@ 8.5G	$R_{X\_SEN2}$			<b>– 11</b>	dBm	Measured with a PRBS 2 <sub>7</sub> -1 test pattern @ 8.5Gbps, BER≤10- <sub>12</sub>
Receiver Sensitivity (OMA)@ 14.025G	$R_{X\_SEN3}$			<b>– 10</b>	dBm	Measured with a PRBS 2₃1 -1 test pattern @ 14.025Gbps, BER≤10-12
Maximum Input Power	$P_{IN}$	0.5			dBm	
Optical Return Loss	ORL			-12	dB	
LOS Assert	$LOS_A$	<b>– 25</b>			dBm	
LOS De-Assert	$LOS_D$			<b>–</b> 12.5	dBm	
LOS Hysteresis		0.5			dB	

### **Electrical Characteristics – Transmitter**

 $V_{CC}$ =3V to 3.6V,  $T_{C}$ =0°C to 70°C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Input differential impedance	$R_{IN}$		100		Ω	Non condensing
Single ended data input swing	$V_{IN\_PP}$	90		800	mV	
Transmit disable voltage	$V_D$	2		V <sub>CC</sub>	V	
Transmit enable voltage	$V_{EN}$	V <sub>EE</sub>		V <sub>EE</sub> +0.	V	
_				8		

## **Electrical Characteristics – Receiver**

 $V_{CC}$ =3V to 3.6V,  $T_{C}$ =0°C to 70°C

Parameter	Symbol	Min	Тур	Max	Unit	Remarks
Single ended data output swing	$V_{OUT\_PP}$	170	300	400	mV	
LOS Fault	$V_{LOS\_Fault}$	2		V <sub>CC_HO</sub>	V	
				ST		
LOS Normal	$V_{LOS\_normal}$	V <sub>EE</sub>		V <sub>EE</sub> +0.	V	
				5		

### **Digital Diagnostic Functions**

QK724A-C support the 2-wire serial communication protocol as defined in the SFF 8472. Digital



diagnostic information are accessible over the 2-wire interface at the address 0xA2. Digital Diagnostics for QK724A-C are internally calibrated by default. A micro controller unit inside the transceiver gathers the monitoring information and reports the status of transceiver.

**Transceiver Temperature**, internally measured, represented as a 16 bit signed twos complement value in increments of 1/256 degrees Celsius, Temperature accuracy is better than ±3 degrees Celsius over specified operating temperature and voltage.

**Transceiver Supply Power,** internally measured, represented as a 16 bit unsigned integer with the voltage defined as the full 16 bit value (0-65535) with LSB equal to 100  $\mu$ Volt, yielding a total range of 0 to +6.55 Volts.


**Transceiver TX bias current,** internally measured, represented as a 16 bit unsigned integer with the current defined as the full 16 bit value (0 - 65535) with LSB equal to 2  $\mu$ A, yielding a total range of 0 to 131mA. Accuracy is better than  $\pm 10\%$  over specified operating temperature and voltage.

**Transceiver TX output power,** internally measured, represented as a 16 bit unsigned integer with the power defined as the full 16 bit value (0-65535) with LSB equal to 0.1  $\mu$ W. Data is assumed to be based on measurement of laser monitor photodiode current. Accuracy is better than  $\pm 3$ dB over specified temperature and voltage. Data is not valid when the transmitter is disabled.

**Transceiver RX received optical power,** internally measured, represented as a 16 bit unsigned integer with the power defined as the full 16 bit 35 value (0-65535) with LSB equal to 0.1  $\mu$ W. Accuracy is better than  $\pm 3$ dB over specified temperature and voltage.

Parameter	Symbol	Accuracy	Units	Repor	t Range	Unit	Remarks
		Inte	ernal Cali	bration			
Temperature	$T_{MON}$	±3	°C	- 5	75	°C	
Voltage	$V_{MON}$	±0.1	V	2.9	3.7	V	
Bias Current	I <sub>MON</sub>	±10	%	1	15	mA	
Tx Power	P <sub>MON</sub>	±3	dB	<b>– 10</b>	0	dBm	
Rx Power	P <sub>MON</sub>	±3	dB	<b>- 20</b>	0	dBm	

#### **Block Diagram of Transceiver**





#### **Transmitter Section**

The VCSEL driver accept differential input data and provide bias and modulation currents for driving a laser. An automatic power-control (APC) feedback loop is incorporated to maintain a constant average optical power. 850 nm VCSEL in an eye safe optical subassembly (OSA) mates to the fiber cable.

### TX\_DISABLE

The TX\_DISABLE signal is high (TTL logic "1") to turn off the laser output. The laser will turn on within 1ms when TX\_DISABLE is low (TTL logic "0").

#### TX FAULT

When the TX\_FAULT signal is high, output indicates a laser fault of some kind. Low indicates normal operation.

### **Receiver Section**

The receiver utilizes a PIN detector integrated with a trans-impedance preamplifier in an OSA. This OSA is connected to a Limiting Amplifier which providing post-amplification quantization, and optical signal detection. The limiting Amplifier is AC-coupled to the transimpedance amplifier, with internal  $100\Omega$  differential termination.

#### Receive Loss (RX\_LOS)


The RX\_LOS is high (logic "1") when there is no incoming light from the companion transceiver. This signal is normally used by the system for the diagnostic purpose. The signal is operated in TTL level.

#### **Controller Section**

The micro controller unit monitors the operation information of LD driver and Limiting Amplifier. And report these status to the customer.


#### **Dimensions**






# ALL DIMENSIONS ARE ±0.2mm UNLESS OTHERWISE SPECIFIED UNIT: mm

## **PCB Layout Recommendation**




- /Datum and Basic Dimension Established by Customer
- Rads and Vias are Chassis Ground, 11 Places
- AThrough Holes are Unplated






## **Electrical Pad Layout**







### **Pin Assignment**

PIN#	Symbol	Description	Remarks					
1	V <sub>EET</sub>	Transmitter ground (common with receiver ground)	Circuit ground is isolated from chassis ground					
2	$T_{FAULT}$	Transmitter Fault.						
3	$T_{DIS}$	Transmitter Disable. Laser output disable on high or open	Disabled: T <sub>DIS</sub> >2V or open Enabled: T <sub>DIS</sub> <0.8V					
4	SDA	Data line for serial ID	Should Be pulled up with					
5	SCL	Clock line for serial ID	4.7k – 10k ohm on					
6	MOD_ABS	Module Absent. Grounded within the module	board to a voltage between 2V and 3.6V					
7	RS0	No connection required						
8	LOS	Loss of Signal indication. Logic 0 indicates normal operation	LOS is open collector output					
9	RS1	No connection required	<u>.                                      </u>					
10	V <sub>EER</sub>	Receiver ground (common with transmitter ground)	Circuit ground is isolated					
11	V <sub>EER</sub>	Receiver ground (common with transmitter ground)	from chassis ground					
12	RD-	Receiver Inverted DATA out. AC coupled						
13	RD+	Receiver Non-inverted DATA out. AC coupled						



14	$V_{EER}$	Receiver ground (common with transmitter ground is isolated from chassis ground
15	$V_{CCR}$	Receiver power supply
16	$V_{CCT}$	Transmitter power supply
17	$V_{EET}$	Transmitter ground (common with receiver connected to chassis ground)
18	TD+	Transmitter Non-Inverted DATA in. AC coupled
19	TD-	Transmitter Inverted DATA in. AC coupled
20	$V_{EET}$	Transmitter ground (common with receiver ground)  Circuit ground is connected to chassis ground

#### References

- 1. IEEE standard 802.3ae. IEEE Standard Department, 2005.
- 2. Enhanced 8.5 and 10 Gigabit Small Form Factor Pluggable Module "SFP+" SFF-8431
- 3. Digital Diagnostics Monitoring Interface for Optical Transceivers SFF-8472.