

**760115394 | MOD-V-48P****Commscope Modular Vertical Outlet Panel, 48 port**

- When equipped with Uniprise UNJ10G Cat6A Outlet or SYSTIMAX® MGS600, MGS500, MGS400 Information Outlet, the MGS Isolation Cap must be added to each outlet within the panel. The Isolation Caps are sold separately.
- Isolation Caps are not required when equipped with Uniprise UNJ600 or UNJ500 Outlets.

Dimensions

Depth	34.29 mm		1.35 in
Diameter Over Dielectric, maximum	1.168 mm		0.046 in
Diameter Over Dielectric, minimum	0.762 mm		0.030 in
Height	88.90 mm		3.50 in
Width	482.60 mm		19.00 in

Electrical Specifications

ANSI/TIA Category	5 5e 6 6A 3
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Total Ports, quantity	48
Cable Type	U/UTP (unshielded)
Product Type	Panel, modular
Brand	CommScope®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2

Mechanical Specifications

Panel Style	Straight
Conductor Gauge, solid	22 AWG 24 AWG
Conductor Gauge, stranded	22 AWG 24 AWG

760115394 | MOD-V-48P

Conductor Type	Solid Stranded (7 strands)
Material Type	High-impact, flame retardant, thermoplastic
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	133 N 30 lbf
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

