




8441704/10 | 10GN4 WHITE REEL

Ultra 10® 10GN4 ETL Verified Category 6A U/UTP Cable, non-plenum, white jacket, 4 pair count, 1000 ft (305 m) length reel

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin
Separator Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	40.60 lb/kft
Diameter Over Jacket	8.001 mm 0.315 in
Jacket Thickness	1.473 mm 0.058 in

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	7.61 ohms/100 m
Mutual Capacitance	6.0 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	65 %
Operating Frequency, maximum	500 MHz
Transmission Standards	ANSI/TIA-568-C.2
Safety Voltage Rating	300 V

8441704/10 | 10GN4 WHITE REEL

Dielectric Strength, minimum 1500 Vac | 2500 Vdc

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	Reel
Brand	Ultra 10® Uniprise®
Jacket Color	White
Product Number	10GN4
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Separator Type	Bisector

Mechanical Specifications

Pulling Tension, maximum 11 kg | 25 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Electrical Performance

- Std Refers to the standard value listed under Transmission Standards in the Electrical Specifications above
- Typ Typical
- IL Insertion Loss (dB/100m)
- NEXT Near End Crosstalk (dB/100m)
- ACR Attenuation to Crosstalk Ratio (dB/100m)
- PSNEXT Power Sum Near End Crosstalk (db/100m)
- PSACR Power Sum Attenuation to Crosstalk Ratio (dB/100m)
- ACRF Attenuation to Crosstalk Ratio - Far End (dB/100m)
- PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
- RL Return Loss (dB)
- TCL Transverse Conversion Loss (dB/100m)
- ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL	ELTCTL
	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Std
1	2.1	1.8	74.3	91.0	72.2	89.2	72.3	89.0	70.2	87.3	67.8	84.5	64.8	82.5	20.0	33.0	40.0	35.0
4	3.8	3.5	65.3	83.1	61.5	79.6	63.3	81.0	59.5	77.5	55.8	72.6	52.8	70.5	23.0	34.6	40.0	23.0
8	5.3	5.0	60.8	79.0	55.4	73.9	58.8	76.9	53.4	71.8	49.7	66.6	46.7	64.4	24.5	37.3	40.0	16.9
10	5.9	5.6	59.3	76.6	53.4	71.0	57.3	74.7	51.4	69.1	47.8	64.7	44.8	62.5	25.0	38.4	40.0	15.0
16	7.5	7.1	56.2	73.6	48.8	66.5	54.2	71.5	46.8	64.3	43.7	60.6	40.7	58.2	25.0	39.6	38.0	10.9
20	8.4	8.0	54.8	73.0	46.4	65.0	52.8	71.0	44.4	63.0	41.8	58.6	38.8	56.2	25.0	38.9	37.0	9.0
25	9.4	9.0	53.3	70.6	44.0	61.7	51.3	68.8	42.0	59.8	39.8	56.5	36.8	54.2	24.3	38.7	36.0	7.0
31.25	10.5	10.1	51.9	68.7	41.4	58.7	49.9	66.9	39.4	56.8	37.9	54.4	34.9	52.1	23.6	39.3	35.1	
62.5	15.0	14.4	47.4	64.6	32.4	50.3	45.4	62.7	30.4	48.3	31.9	48.5	28.9	46.0	21.5	36.3	32.0	
100	19.1	18.4	44.3	60.2	25.2	41.9	42.3	58.7	23.2	40.4	27.8	44.5	24.8	42.2	20.1	35.8	30.0	
155	24.1	23.2	41.4	60.8	17.4	37.7	39.4	58.8	15.4	35.6	24.0	41.0	21.0	38.7	18.8	33.1	28.1	
200	27.6	26.5	39.8	56.8	12.2	30.4	37.8	55.0	10.2	28.5	21.8	38.5	18.8	36.3	18.0	33.0	27.0	
250	31.1	29.8	38.3	54.8	7.3	25.1	36.3	52.8	5.3	23.0	19.8	36.5	16.8	34.2	17.3	32.6	26.0	
300	34.3	32.9	37.1	53.4	2.9	20.5	35.1	51.4	0.9	18.5	18.3	35.0	15.3	32.5	16.8	32.5	25.2	
350	37.2	35.7	36.1	52.1	-1.1	16.4	34.1	50.1	-3.1	14.4	16.9	34.0	13.9	31.4	16.3	33.2	24.6	
400	40.1	38.2	35.3	50.4	-4.8	12.2	33.3	48.3	-6.8	10.1	15.8	32.0	12.8	30.0	15.9	34.2	24.0	
500	45.3	43.1	33.8	47.3	-11.4	4.2	31.8	45.5	-13.4	2.4	13.8	29.9	10.8	27.8	15.2	34.6	23.0	
650		49.8		43.1		-6.6		41.3		-8.4		27.4		25.1		27.2		