


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART NUMBER	FIBER TYPE	WEIGHT
FIID102	62.5/200/230 OM1 POLYMER COATED FIBER	12 kg/km (8.1 lbs/km)
FIID202	50/200/230 OM2 POLYMER COATED FIBER	

TECHNICAL SPECIFICATIONS			
MAXIMUM ATTENUATION			
850nm		1300nm	
5dB/km		3dB/km	
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
111 N (25 lbs)	22 N (5 lbs)	33mm (1.30 in)	22mm (.87 in)
TEMPERATURE			
INSTALLATION/OPERATION		STORAGE	
-20°C TO 105°C -4°F TO 221°F		-40°C TO 80°C -40°F TO 176°F	

NOTES:

- CABLE JACKET MEETS UL1666 FOR RISER RATING AND THE REQUIREMENTS OF IEC 60332, IEC 61034 AND IEC 60754 FOR LSZH FLAME RATING.
- CABLE SUPPLIED IN MINIMUM 500 METER (1640 FT.) LENGTHS.
- DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS (in) ARE ENGLISH.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

							TITLE FIBER OPTIC INDUSTRIALNET ZIPCORD PCF CABLE CUSTOMER DRAWING					
							ITEM REVISION NAME 11F159EE/00 PCF ZIPCORD CABLE			<div>PANDUIT</div>		
							DATASET FILE NAME 11F159EE_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 (2.54) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5 ° <div></div> THIRD ANGLE PROJECTION					
							MATERIAL: SEE NOTE 5					
							DRAWING NUMBER: 11F159EE-DC					
R	09-18-12	SAT	WMA	TCB	RELEASED TO PRODUCTION	11F159EE-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE A
							MC	07-10-12	WMA	NONE		