




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

**NOTES:**

1. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
2. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
3. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596.
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



						TITLE	
						12 FIBER MPO TO LC LSZH TRUNK CABLE WITH PULLING EYE	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	PANDUIT
						12F178BM/00	
						DATASET FILE NAME	
						12F178BM_DC/00A	MATERIAL:
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.X ± .xxx ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±	
						 THIRD ANGLE PROJECTION	DRAWING NUMBER: 12F178BM-DC
00	08-26-13	SAT	WMA		RELEASED TO PRODUCTION	12F178BM-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT
							DATE 08-26-13
							CHK WMA
							SCALE NONE
							SHT 1 OF 3
							SIZE A

