





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



WYR-GRID CENTER SUPPORT BRACKET




1200 DEPTH STRUT

FIBERRUNNER/WYR-GRID
QUICKLOCK CLIP ASSEMBLY

PANDUIT PART NUMBER	WEIGHT
WGCMK1200**	11.25 LBS (5.10 kg)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- THE WYR-GRID CABINET MOUNT BRACKET 1200 KIT PACKAGE CONTAINS THE FOLLOWING:
 ONE (1) WYR-GRID CENTER SUPPORT BRACKET
 TWO (2) WYR-GRID UPRIGHT SUPPORT BRACKETS
 TWO (2) WYR-GRID/FIBERRUNNER QUICKLOCK CLIP ASSEMBLY
 ONE (1) TOP OF CABINET 1200 DEPTH STRUT ASSEMBLY
 TWO (2) M10 X 1.5 X 30 SOCKET HEAD CAP SCREW
 TWO (2) M10 HELICAL SPRING LOCKWASHER
 FOUR (4) M5 BUTTON HEAD TORX SCREWS
- ALL DIMENSIONS IN PARENTHESES ARE INCHES.



							TITLE WYR-GRID CABINET MOUNT BRACKET 1200 (WGCMK1200**) CUSTOMER DRAWING						
							ITEM REVISION NAME 14D419AG/01						
							DATASET FILE NAME 14D419AG-DC/01A WGCMK1200**						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				MATERIAL:		
							INCHES X.X +/- 0.18 X.XX +/- 0.10 X.XXX +/- 0.036		METRIC - MILLIMETER X +/- 4.57 X.X +/- 2.54 X.XX +/- 0.92		ANGLE +/- 1°		
01A	12-16-14	TWV	DWR		RELEASED TO PRODUCTION		 THIRD ANGLE PROJECTION					DRAWING NUMBER: 14D419AG-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TWV		DATE 12-16-14	CHK DWR	SCALE NONE	SHT 1 OF 1	SIZE A