

2




1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
GMPO-A0276BL	X.XXkg (X.XXlb)

- NOTES:
- IDENTIFICATION: HORIZONTAL, MIXED (6) LOCKING C13 & (2) LOCKING C19, GATEWAY-ENABLED MONITORED WITH MONITORED PER OUTLET, 208V / 30A / SINGLE-PHASE PDU
  - ACCESSORY COMPONENTS:
    - (1) QUICK-START GUIDE
    - (4) M6 × 15mm MOUNTING SCREWS
    - (4) #12-24 × 1/2" MOUNTING SCREWS
  - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [ INCHES ]
  - INPUT POWER (AMPS, VOLTS, kVA, POWER FACTOR, FREQUENCY) MONITORING. DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY
  - OUTLET LEVEL POWER (AMPS, VOLTS, POWER FACTOR, FREQUENCY) MONITORING CAN BE ACCESSED REMOTELY VIA SERIAL CONNECTION TO GATWAY
  - RoHS COMPLIANT
  - VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
  - MAXIMUM AVAILABLE INPUT POWER = 5.0 kW
  - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODE
  - PRINTED WITH PHASE & CIRCUIT IDENTIFICATION


PART NO.                    COLOR  
GMPO-A0276BL            BLACK



REAR VIEW



FRONT VIEW



SIDE VIEW

PLUG  
30 AMP, 250V  
TWIST-LOCK  
NEMA L6-30P

SIX (6)  
LOCKING RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13

TWO (2)  
LOCKING RECEPTACLES  
20 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

01A	03/10/15	PJST	GLM	EDM	REVISED DISPLAY ORIENTATION	AA0276CP
00A	12/08/14	MIM	GLM	EDM	RELEASED TO PRODUCTION	AA0276CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
SMARTZONE GATEWAY-ENABLED MPO SERIES RACK PDU			
GMPO-A0276BL			
CUSTOMER DRAWING			
ITEM REVISION NAME			
AA0276AP/01.PRT			
DATASET FILE NAME		MATERIAL/COLOR:	
AA0276CP_DC/01A.PRT		N/A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		DRAWING NUMBER:	
INCHES: X.X +/-, X.XX +/-, X.XXX +/-		METRIC: MILLIMETER X.X +/-, X.XX +/-	
THIRD ANGLE PROJECTION		AA0276CP_DC	
DRAWN BY	DATE	CHK	SCALE
MIM	12/08/14	GLM	NONE
SHT 1 OF 1		SIZE B	