




PANDUIT P/N	WEIGHT
GM-A0924BL	5 kg (11 lb)



TOP VIEW



SIDE VIEW



FRONT VIEW

NOTES:  
1. IDENTIFICATION: GATEWAY MONITORED ZERO-RU INLINE METER,  
(1) 20A NEMA L6-20P, 208V / 20A / SINGLE-PHASE PDU

PART NO. GM-A0924BL  
COLOR BLACK RAL 9005

2. ACCESSORY COMPONENTS:
- (4) M6 x 12mm MOUNTING SCREWS
  - (4) M6 x 12mm MOUNTING SCREWS
  - (4) M6 NUT (CAGED)
  - (1) M5 NUT (NYLON INSERT)
  - (1) M5 LOCK WASHER

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]


4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.

5. RoHS COMPLIANT.


6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

7. MAXIMUM AVAILABLE INPUT POWER = 3.3 kW

8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



00A	09/10/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0924CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.			SIGN										
			DATE										
			PRINT										
TITLE													
SmartZone Gateway-Enabled Zero-RU Inline Meter PN: GM-A0924BL CUSTOMER DRAWING													
ITEM REVISION NAME		<b>PANDUIT</b>											
AA0924CP/00.PRT													
DATASET FILE NAME		BLACK RAL 9005 TEXTURE FINISH											
AA0924CP_DS/00A.PRT													
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:											
<table><tr><td>INCHES</td><td>METRIC - MILLIMETER</td><td>ANGLE</td></tr><tr><td>X.X +/- 0.03</td><td>X.X +/- 0.8</td><td rowspan="3">+/- 1°</td></tr><tr><td>X.XX +/- 0.018</td><td>X.XX +/- 0.46</td></tr><tr><td>X.XX +/- 0.007</td><td>X.XX +/- 0.18</td></tr></table>		INCHES	METRIC - MILLIMETER	ANGLE	X.X +/- 0.03	X.X +/- 0.8	+/- 1°	X.XX +/- 0.018	X.XX +/- 0.46	X.XX +/- 0.007	X.XX +/- 0.18		
INCHES	METRIC - MILLIMETER	ANGLE											
X.X +/- 0.03	X.X +/- 0.8	+/- 1°											
X.XX +/- 0.018	X.XX +/- 0.46												
X.XX +/- 0.007	X.XX +/- 0.18												
		THIRD ANGLE PROJECTION											
DRAWN BY		DRAWING NUMBER:											
DACU		AA0924CP											
DATE	CHK	SCALE	SIZE										
09/10/14	JPHI	SCALE:1:5	SHEET 1 OF 1 B										