



TOP VIEW



FRONT VIEW



SIDE VIEW


Panduit P/N	Weight
GM-A0936BL	8.5 kg (19 lb)

NOTES:
1. INDENTIFICATION: GATEWAY MONITORED 1-RU INLINE METER,
(1) 20A IEC60309, 208 / 20A / SINGLE - PHASE PDU


PART NO. GM-A0936BL
COLOR BLACK RAL 9005

2. ACCESSORY COMPONENTS:
- (4) M6 x 12mm PAN HEAD MACHINE SCREWS
 - (4) M6 x 12mm PAN HEAD SELF-TAPPING SCREWS
 - (4) M6 NUT (CAGED)
 - (1) M5 NUT (NYLON INSERT)
 - (1) M5 LOCK WASHER

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 3.3 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



00A	02/10/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0936CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.				SIGN	
				DATE	
				PRINT	
TITLE					
SmartZone Gateway-Enabled 1RU Inline Meter PN: GM-A0936BL CUSTOMER DRAWING					
ITEM REVISION NAME AA0936CP/00.PRT				PANDUIT®	
DATASET FILE NAME AA0936CP_DS/00A.PRT					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:				MATERIAL/COLOR:	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		METRIC - MILLIMETER X +/- 0.8 X.X +/- 0.46 X.XXX +/- 0.18		BLACK RAL 9005 TEXTURE FINISH	
		THIRD ANGLE PROJECTION		DRAWING NUMBER: AA0936CP	
DRAWN BY DACU	DATE 02/10/14	CHK JPHI	SCALE SCALE:1:7	SHEET 1 OF 1	
				SIZE B	