



TOP VIEW



FRONT VIEW



SIDE VIEW

Panduit P/N	Weight
GM-A0945BL	8.5 kg (19 lb)

NOTES:
1. IDENTIFICATION: GATEWAY MONITORED 1 RU INLINE METER,
(1) NEMA L5-20P, 120V / 20A / SINGLE PHASE PDU

PART NO. GM-A0945BL
COLOR BLACK RAL 9005

2. ACCESSORY COMPONENTS:
(4) M6 x 12mm PAN HEAD MACHINE SCREWS
(4) M6 x 12mm PAN HEAD SELF-TAPPING SCREWS
(4) M6 NUT (CAGED)
(1) M5 NUT (NYLON INSERT)
(1) M5 LOCK WASHER

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS
APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 1.9 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.	SIGN
	DATE
	PRINT

TITLE SmartZone Gateway-Enabled 1RU Inline Meter PN: GM-A0945BL CUSTOMER DRAWING	
ITEM REVISION NAME AA0945CP/00.PRT	
DATASET FILE NAME AA0945CP_DS/00A.PRT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007 METRIC - MILLIMETER X.X +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18 ANGLE +/- 1°	MATERIAL/COLOR: BLACK RAL 9005 TEXTURE FINISH
 THIRD ANGLE PROJECTION	DRAWING NUMBER: AA0945CP

DRAWN BY DACU	DATE 10/07/14	CHK JPHI	SCALE SCALE:1:7	SHEET 1 OF 1	SIZE B
------------------	------------------	-------------	--------------------	--------------	-----------

PLUG
20 AMP, 125V
TWIST LOCK
NEMA L5-20P

RECEPTACLE
20 AMP, 125V
TWIST LOCK
NEMA L5-20R

00A	10/07/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0945CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN