



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
Q1N2B1P3N30AHA0	10.1 kg (22.3 lb)

- NOTES:
- IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19, NETWORKED 208V / 30A / THREE-PHASE WYE PDU
  - PART NO. Q1N2B1P3N30AHA0      COLOR BLACK
  - ACCESSORY COMPONENTS: (1) QUICK-START GUIDE
  - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
  - PHASE (XY, YZ, ZX) AND CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
  - RoHS COMPLIANT.
  - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
  - MAXIMUM AVAILABLE INPUT POWER = 8.6 kW
  - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

B




A

PLUG  
30 AMP, 120/208V × 3- WYE  
TWIST LOCK  
NEMA L21-30P

TWENTY-FOUR (24)  
RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13

SIX (6)  
RECEPTACLES  
20 AMP, 230V  
STRAIGHT BLADE  
IEC 60320/C19

02A	5-21-14	PIP	MRWA	EDM	RELEASED TO PRODUCTION	12V091TX-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN



B

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
Q1N2B1P3N30AHA0			
CUSTOMER DRAWING			
ITEM REVISION NAME		12V091TX/02.PRT	
DATASET FILE NAME		12V091TX_DC/02A.PRT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	ANGLE	
X.X +/- 0.03	X. +/- 0.8	+/- 1°	
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY PIP		12V091TX-DC	
DATE 5-21-14	CHK MRWA	SCALE NONE	SIZE B
SHT 1 OF 1			