


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NO.	WEIGHT CABINET ONLY
CQSMDC79	550 LBS/EACH 159 Kg/EACH

# NOTES:



- INCLUDED WITH SYSTEM:
  - BONDING CAGE NUTS
  - CAGE NUTS FOR EQUIPMENT MOUNTING
  - 2RU TOOL-LESS BLANKING PANELS
  - 1RU TOOL-LESS BLANKING PANELS
  - 2RU PERFORATED PANELS
  - (4) ANGLED 48-PORT PATCH PANELS
  - 15 FEET OF HOOK AND LOOP
  - D-RINGS FOR VERTICAL CABLE MANAGEMENT
  - HORIZONTAL CABLE MANAGERS
  - 19 INCH GROUNDING BUSBAR
  - GROUNDING WIRE FOR CABINET
  - ADJUSTABLE FABRIC ESD WRIST STRAP
  - 12 UTP CABLES (2 BLACK, 5 WHITE, AND 5 BLUE)
  - DYNAMIC PALLET TO PROTECT ANY EQUIPMENT INSTALLED PRIOR TO SHIPMENT.
- FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
- STATIC LOAD RATING: 2500 LBS [1134 kg].
- DYNAMIC LOAD RATING: 1250 LBS [568 kg].
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.



PERFORATED FRONT  
SINGLE HINGE DOOR  
FRONT-LEFT ISO VIEW



PERFORATED  
REAR SPLIT DOOR  
REAR-RIGHT ISO VIEW

							TITLE						
							CQSMDC79 - CUSTOMER DRAWING						
							CONTROL DRAWING						
							ITEM REVISION NAME						
							12V304CF/00.PRT						
							DATASET FILE NAME		MATERIAL/COLOR:  N/A				
							12V304CF_DC/00A.PRT						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:						
							INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007						
							METRIC - MILLIMETER X. +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18		ANGLE +/- 1°				
									DRAWING NUMBER: 12V304CF				
							THIRD ANGLE PROJECTION						
OOA	5-1-13	NWW		TIMH	RELEASED TO PRODUCTION	12V304CF	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1	SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	NWW	5-1-13	TIMH		1:25		A