


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

B

←

A




PANDUIT P/N	"W"	"X"	WEIGHT
PEVF696B1	6.0	2	34.00 LBS/EACH (15.42 KG/EACH)
PEVF896B1	8.0	3	35.02 LBS/EACH (15.88 KG/EACH)
PEVF1096B1	10.0	4	35.92 LBS/EACH (16.29 KG/EACH)
PEVF1296B1	12.0	6	36.89 LBS/EACH (16.73 KG/EACH)

B

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) SINGLE-SIDE 96" VERTICAL MANAGER
(1) HARDWARE KIT
(4) LEFT 10" FINGERS
(4) RIGHT 10" FINGERS
(1) LEFT 11" FINGERS
(1) RIGHT 11" FINGERS
(2) DOOR BRACKET BASES
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 3 ROWS OF "X" RU 19" CEA OPENINGS.
- DOOR SOLD SEPARATELY.
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

TITLE PATCHRUNNER HIGH CAPACITY VERTICAL MANAGER- 96" TALL, SINGLE SIDED (PEVF*96B1)						CONTROL DRAWING	
ITEM REVISION NAME 11V260AG/00							
DATASET FILE NAME 11V260AG_DC/00A							
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				MATERIAL: BACKBONE: STEEL FINGERS: ABS			
				DRAWING NUMBER: 11V260AG			
DRAWN BY FGR		DATE 10/17/13		CHK BAME		SCALE NONE	
THIRD ANGLE PROJECTION						SIZE A	
SHT 1 OF 1							

A